


## CRIMPING COMPRESSION TOOL DIE, TYPE ML, HEAVY-DUTY DIN46235, #3 STRANDED-4/0 STRANDED, 25 MM<sup>2</sup> STRANDED-95 MM<sup>2</sup> STRANDED

### 目录编号

**PKML2529**



### 功能

Suitable for cable lugs and connectors

### 产品属性

Article Number: 716995

Lug/Connector Type: Heavy-Duty DIN46235

Conductor Size: #3 Stranded - 4/0 Stranded; 25 mm<sup>2</sup> Stranded - 95 mm<sup>2</sup> Stranded

Crimping Width: 5mm

Tool: MLB

### 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:  
[nVent.com](https://www.nVent.com) CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.