

19" FAN UNIT, 1 U, REMOTE CONTROL AND MONITORING

风扇单元带 ModBus 接口,适合安装在机柜的 1 U 空间内

功能

支持风扇速度温度监控

适用于远程监控和控制的 ModBus 接口

前面板上的风扇控制装置可调节温度阈值

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included

SPECIFICATIONS

Table 1/2

物料号	气流	噪音等级	电源	最大静压	环境温度	Lifespan, L10 @ 40 C
10713-554	1089 m ³ /h	59.5 dB(A)	97 W	78 Pa	-10 to 70 °C	99558 h

Table 2/2

物料号	产品类型	交流输入电压
10713-554	风扇单元	100 – 240 V

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:
[nVent.com](https://www.nVent.com) CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.