


CABLE TO CABLE, RAIL



nVent ERICO Cadweld applications for railway properties utilize the nVent ERICO Cadweld Plus F80 and the nVent ERICO Cadweld F80 welding material alloys. nVent ERICO Cadweld exothermically welded connections are engineered to provide a permanent, molecular bond that will not loosen or corrode, enabling connection of dissimilar materials. The connections are designed to perform for the life of the conductor and/or installation. The nVent ERICO Cadweld connection has a current carrying capacity equal to or greater than that of the conductor and will withstand repeated fault currents without failing during operation. Once completed, installers can clearly ensure quality by visually inspecting the new connection.

FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

SPECIFICATIONS

Table 1/2

Catalog Number	Mold Family	Price Key	Handle Clamp	Welding Material	Conductor 2	Conductor 1 Outer Diameter, Nominal
PB10PA1G1G	PA Mold Family	C	L160, Sold Separately	SB32 or SB32PLUSF80, Sold Separately	#6 Solid	4.11mm
SB02SS6	SS Mold Family	T	Mini EZ Attached	SB25 or SB25PLUSF80, Sold Separately	#6 Solid	4.11mm
SB10SS1H1G	SS Mold Family	C	L160, Sold Separately	SB25 or SB25PLUSF80, Sold Separately	#6 Solid	4.67mm

Catalog Number	Mold Family	Price Key	Handle Clamp	Welding Material	Conductor 2	Conductor 1 Outer Diameter, Nominal
PB10PC2C1H	PC Mold Family	C	L160, Sold Separately	PB45 or PB45PLUSF80, Sold Separately	#6 Concentric	9.47mm
PB10SS2Q1H	SS Mold Family	C	L160, Sold Separately	PB65 or PB65PLUSF80, Sold Separately	#6 Concentric	13.41mm
PB20TA2G1H	TA Mold Family	C	L160, Sold Separately	PB45 or PB45PLUSF80, Sold Separately	#6 Concentric	10.62mm
PB20TA2Q1H	TA Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	#6 Concentric	13.41mm
SB10SS1V3	SS Mold Family	C	L160, Sold Separately	SB32 or SB25PLUSF80, Sold Separately	3/16 Signal	7.42mm
PB10SS2Q1L	SS Mold Family	C	L160, Sold Separately	PB65 or PB65PLUSF80, Sold Separately	#4 Concentric	13.41mm
PB20TA1L2V	TA Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	250 kcmil Concentric	5.89mm
PB20TA2V1L	TA Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	#4 Concentric	14.61mm
PB10SS1T	SS Mold Family	C	L160, Sold Separately	SB32 or SB32PLUSF80, Sold Separately	#2 Solid	6.53mm
PB20TA2Q1V	TA Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	#2 Concentric	13.41mm
SB10SS1V	SS Mold Family	C	L160, Sold Separately	SB32 or SB25PLUSF80, Sold Separately	#2 Concentric	7.42mm
PB10SS1Y	SS Mold Family	C	L160, Sold Separately	SB32 or SB32PLUSF80, Sold Separately	#1 Concentric	8.43mm
PB20PAY3Y3	PA Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	50 mm ² Concentric	8.99mm
PB20TAT2Y3	TA Mold Family	C	L160, Sold Separately	PB150 or PB150PLUSF80, Sold Separately	50 mm ² Concentric	10mm

Catalog Number	Mold Family	Price Key	Handle Clamp	Welding Material	Conductor 2	Conductor 1 Outer Diameter, Nominal
PB10SS2C	SS Mold Family	C	L160, Sold Separately	PB45 or PB45PLUSF80, Sold Separately	1/0 Concentric	9.47mm
PB10SS2Q2C	SS Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	1/0 Concentric	13.41mm
PB20PP2CPS	PP Mold Family	C	L160, Sold Separately	PB45 or PB45PLUSF80, Sold Separately	B154A Plug	9.47mm
PB20TA2C2C	TA Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	1/0 Concentric	9.47mm
PB10PT2G2G	PT Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	2/0 Concentric	10.62mm
PB10SS2G	SS Mold Family	C	L160, Sold Separately	PB65 or PB65PLUSF80, Sold Separately	2/0 Concentric	10.62mm
PB10SS2Q2G	SS Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	2/0 Concentric	13.41mm
PB20PG2G2G	PG Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	2/0 Concentric	10.62mm
PB20PP2GPS	PP Mold Family	C	L160, Sold Separately	PB45 or PB45PLUSF80, Sold Separately	B154A Plug	10.62mm
PB20TA2G2G	TA Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	2/0 Concentric	10.62mm
PB20TA2Q2G	TA Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	2/0 Concentric	13.41mm
PB99XB2Q2G	XB Mold Family	M		PB200 or PB200PLUSF80, Sold Separately	2/0 Concentric	13.41mm
PB10SS2J	SS Mold Family	C	L160, Sold Separately	PB65 or PB65PLUSF80, Sold Separately	2/0 Ropelay	12.19mm
PB20PPS6PS	PP Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	B154A Plug	14.53mm

Catalog Number	Mold Family	Price Key	Handle Clamp	Welding Material	Conductor 2	Conductor 1 Outer Diameter, Nominal
PB10PC2Q2S	PC Mold Family	C	L160, Sold Separately	PB150 or PB150PLUSF80, Sold Separately	4/0 Ropelay	13.41mm
PB10SS2Q	SS Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	4/0 Concentric	13.41mm
PB10SS2S2Q	SS Mold Family	C	L160, Sold Separately	PB90 or PB90PLUSF80, Sold Separately	4/0 Concentric	15.49mm
PB10SS2V2Q	SS Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	4/0 Concentric	14.61mm
PB13SV2Q	SV Mold Family	R	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	4/0 Concentric	13.41mm
PB20TA2Q2Q	TA Mold Family	C	L160, Sold Separately	PB150 or PB150PLUSF80, Sold Separately	4/0 Concentric	13.41mm
PB20TA2Q4R	TA Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	1100/#24 Ropelay	13.41mm
PB20TAS5S5	TA Mold Family	C	L160, Sold Separately	PB150 or PB150PLUSF80, Sold Separately	2/0 Composite	13.36mm
PB99XB2Q2Q	XB Mold Family	M		PB250 or PB250PLUSF80, Sold Separately	4/0 Concentric	13.41mm
PB10PTS6S6	PT Mold Family	C	L160, Sold Separately	PB250 or PB250PLUSF80, Sold Separately	3/0 Composite	14.53mm
PB10SS2V	SS Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	250 kcmil Concentric	14.61mm
PB10SS2W2V	SS Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	250 kcmil Concentric	19.05mm
PB10SSS6	SS Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	3/0 Composite	14.53mm
PB20TA2V2V	TA Mold Family	C	L160, Sold Separately	PB150 or PB150PLUSF80, Sold Separately	250 kcmil Concentric	14.61mm

Catalog Number	Mold Family	Price Key	Handle Clamp	Welding Material	Conductor 2	Conductor 1 Outer Diameter, Nominal
PB99XB2V2V	XB Mold Family	M		PB150 x 2 or PB300PLUSF80, Sold Separately	250 kcmil Concentric	14.61mm
PB99XB2V2VM	XB Mold Family	M		PB150 x 2 or PB300PLUSF80, Sold Separately	250 kcmil Concentric	14.61mm
PB10SS2S	SS Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	4/0 Ropelay	15.49mm
PB10SS2W3DC	SS Mold Family	C	L160, Sold Separately	PB150 or PB150PLUSF80, Sold Separately	350 kcmil Compact	19.05mm
PB10SS3SS7	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	4/0 Composite	26.42mm
PB10SSS7	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	4/0 Composite	16.66mm
PB10SS4K2W	SS Mold Family	C	L160, Sold Separately	PB150 or PB150PLUSF80, Sold Separately	250 kcmil Ropelay	16.92mm
PB10SS3D	SS Mold Family	C	L160, Sold Separately	PB150 or PB150PLUSF80, Sold Separately	350 kcmil Concentric	17.3mm
PB10SS3Q3D	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	350 kcmil Concentric	20.65mm
PB10SS3S3D	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	350 kcmil Concentric	26.42mm
PB10SS3QC3S	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	500 kcmil Ropelay	18.62mm
PB10SS3S3QC	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	500 kcmil Compact	26.42mm
PB20TA3QC3QC	TA Mold Family	C	L160, Sold Separately	PB150 x 2 or PB300PLUSF80, Sold Separately	500 kcmil Compact	18.62mm
PB10SS2W	SS Mold Family	C	L160, Sold Separately	PB115 or PB115PLUSF80, Sold Separately	250 kcmil Ropelay	19.05mm

Catalog Number	Mold Family	Price Key	Handle Clamp	Welding Material	Conductor 2	Conductor 1 Outer Diameter, Nominal
PB10SS2W3S	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	500 kcmil Ropelay	19.05mm
PB10SS3S4M	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	775 kcmil/#24 Ropelay	26.42mm
PB20TA2W3S	TA Mold Family	C	L160, Sold Separately	PB250 or PB250PLUSF80, Sold Separately	500 kcmil Ropelay	19.05mm
PB50PC3S2W	PC Mold Family	D	L159, Sold Separately	PB500 or PB500PLUSF80, Sold Separately	250 kcmil Ropelay	26.42mm
PB50PC5A2W	PC Mold Family	D	L159, Sold Separately	SCB7501A, Sold Separately	250 kcmil Ropelay	33.78mm
PB50SS5A2W	SS Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	250 kcmil Ropelay	33.78mm
PB10SS3B3S	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	500 kcmil Ropelay	20.32mm
PB10SS3Q	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	500 kcmil Concentric	20.65mm
PB10SS3S3Q	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	500 kcmil Concentric	26.42mm
PB20TA3Q3Q	TA Mold Family	C	L160, Sold Separately	PB150 x 2 or PB300PLUSF80, Sold Separately	500 kcmil Concentric	20.65mm
PB60TA3Q4Y	TA Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	1000 kcmil Concentric	20.65mm
PB60TA4Y3Q	TA Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	500 kcmil Concentric	29.26mm
PB63TA6H3Q	TA Mold Family	F	L159, Sold Separately	PB250 x 3 or PB750PLUSF80, Sold Separately	500 kcmil Concentric	40.94mm
PB80PG5T3Q	PG Mold Family	K		SCB8002A, Sold Separately	500 kcmil Concentric	35.86mm

Catalog Number	Mold Family	Price Key	Handle Clamp	Welding Material	Conductor 2	Conductor 1 Outer Diameter, Nominal
PB10SS3S3F	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	350 kcmil Ropelay	26.42mm
PB10SS4R	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	1100/#24 Ropelay	22.4mm
PB20TA4R4R	TA Mold Family	C	L160, Sold Separately	PB150 x 2 or PB300PLUSF80, Sold Separately	1100/#24 Ropelay	22.4mm
PB10SS3S4T	SS Mold Family	C	L160, Sold Separately	PB250 or PB250PLUSF80, Sold Separately	1325/#24 Ropelay	26.42mm
PB31TA4T4T	TA Mold Family	D	L159, Sold Separately	PB500 or PB500PLUSF80, Sold Separately	1325/#24 Ropelay	24.94mm
PB50SS4L4T	SS Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	1325/#24 Ropelay	25.35mm
PB10SS4L	SS Mold Family	C	L160, Sold Separately	PB150 x 2 or PB300PLUSF80, Sold Separately	750 kcmil Concentric	25.35mm
PB50SS4L3S	SS Mold Family	D	L159, Sold Separately	PB150 x 2 or PB300PLUSF80, Sold Separately	500 kcmil Ropelay	25.35mm
PB80PA5T4L	PA Mold Family	K		SCB10002A, Sold Separately	750 kcmil Concentric	35.86mm
PB10SS3S	SS Mold Family	C	L160, Sold Separately	PB200 or PB200PLUSF80, Sold Separately	500 kcmil Ropelay	26.42mm
PB10SS3S4X	SS Mold Family	C	L160, Sold Separately	PB150 x 2 or PB300PLUSF80, Sold Separately	1600/#24 Ropelay	26.42mm
PB20TA3S3S	TA Mold Family	C	L160, Sold Separately	PB150 x 2 or PB300PLUSF80, Sold Separately	500 kcmil Ropelay	26.42mm
PB50PC3S5A	PC Mold Family	D	L159, Sold Separately	SCB7501A, Sold Separately	1000 kcmil Ropelay	26.42mm
PB50SS3S4N	SS Mold Family	D	L159, Sold Separately	PB150 x 2 or PB300PLUSF80, Sold Separately	750 kcmil Ropelay	26.42mm

Catalog Number	Mold Family	Price Key	Handle Clamp	Welding Material	Conductor 2	Conductor 1 Outer Diameter, Nominal
PB50SS3S4Y	SS Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	1000 kcmil Concentric	26.42mm
PB50SS3S5A	SS Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	1000 kcmil Ropelay	26.42mm
PB60TA4N3S	TA Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	500 kcmil Ropelay	29.34mm
PB60TA4X4X	TA Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	1600/#24 Ropelay	27.18mm
PB50SS4Y	SS Mold Family	D	L159, Sold Separately	PB200 x 2 or PB400PLUSF80, Sold Separately	1000 kcmil Concentric	29.26mm
PB50SS4N	SS Mold Family	D	L159, Sold Separately	PB500 or PB500PLUSF80, Sold Separately	750 kcmil Ropelay	29.34mm
PB50PC5A5A	PC Mold Family	D	L159, Sold Separately	SCB12502A, Sold Separately	1000 kcmil Ropelay	33.78mm
PB50SS5A	SS Mold Family	D	L159, Sold Separately	PB500 or PB500PLUSF80, Sold Separately	1000 kcmil Ropelay	33.78mm
PB53SS6H	SS Mold Family	F	L159, Sold Separately	SCB10001A, Sold Separately	2000 kcmil Concentric	40.94mm

Table 2/2		
Catalog Number	Conductor 2 Outer Diameter, Nominal	Conductor 1
PB10PA1G1G	4.11mm	#6 Solid
SB02SS6	4.11mm	#6 Solid
SB10SS1H1G	4.11mm	#6 Concentric
PB10PC2C1H	4.67mm	1/0 Concentric
PB10SS2Q1H	4.67mm	4/0 Concentric
PB20TA2G1H	4.67mm	2/0 Concentric
PB20TA2Q1H	4.67mm	4/0 Concentric
SB10SS1V3	4.76mm	#2 Concentric
PB10SS2Q1L	5.89mm	4/0 Concentric
PB20TA1L2V	14.61mm	#4 Concentric

Catalog Number	Conductor 2 Outer Diameter, Nominal	Conductor 1
PB20TA2V1L	5.89mm	250 kcmil Concentric
PB10SS1T	6.53mm	#2 Solid
PB20TA2Q1V	7.42mm	4/0 Concentric
SB10SS1V	7.42mm	#2 Concentric
PB10SS1Y	8.43mm	#1 Concentric
PB20PAY3Y3	8.99mm	50 mm ² Concentric
PB20TAT2Y3	8.99mm	10.0 mm Ground Wire
PB10SS2C	9.47mm	1/0 Concentric
PB10SS2Q2C	9.47mm	4/0 Concentric
PB20PP2CPS	12.7mm	1/0 Concentric
PB20TA2C2C	9.47mm	1/0 Concentric
PB10PT2G2G	10.62mm	2/0 Concentric
PB10SS2G	10.62mm	2/0 Concentric
PB10SS2Q2G	10.62mm	4/0 Concentric
PB20PG2G2G	10.62mm	2/0 Concentric
PB20PP2GPS	12.7mm	2/0 Concentric
PB20TA2G2G	10.62mm	2/0 Concentric
PB20TA2Q2G	10.62mm	4/0 Concentric
PB99XB2Q2G	10.62mm	4/0 Concentric
PB10SS2J	12.19mm	2/0 Ropelay
PB20PPS6PS	12.7mm	3/0 Composite
PB10PC2Q2S	15.49mm	4/0 Concentric
PB10SS2Q	13.41mm	4/0 Concentric
PB10SS2S2Q	13.41mm	4/0 Ropelay
PB10SS2V2Q	13.41mm	250 kcmil Concentric
PB13SV2Q	13.41mm	4/0 Concentric
PB20TA2Q2Q	13.41mm	4/0 Concentric
PB20TA2Q4R	22.4mm	4/0 Concentric
PB20TAS5S5	13.36mm	2/0 Composite
PB99XB2Q2Q	13.41mm	4/0 Concentric
PB10PTS6S6	14.53mm	3/0 Composite
PB10SS2V	14.61mm	250 kcmil Concentric
PB10SS2W2V	14.61mm	250 kcmil Ropelay
PB10SSS6	14.53mm	3/0 Composite

Catalog Number	Conductor 2 Outer Diameter, Nominal	Conductor 1
PB20TA2V2V	14.61mm	250 kcmil Concentric
PB99XB2V2V	14.61mm	250 kcmil Concentric
PB99XB2V2VM	14.61mm	250 kcmil Concentric
PB10SS2S	15.49mm	4/0 Ropelay
PB10SS2W3DC	15.88mm	250 kcmil Ropelay
PB10SS3SS7	16.66mm	500 kcmil Ropelay
PB10SSS7	16.66mm	4/0 Composite
PB10SS4K2W	19.05mm	650/#24 Ropelay
PB10SS3D	17.3mm	350 kcmil Concentric
PB10SS3Q3D	17.3mm	500 kcmil Concentric
PB10SS3S3D	17.3mm	500 kcmil Ropelay
PB10SS3QC3S	26.42mm	500 kcmil Compact
PB10SS3S3QC	18.62mm	500 kcmil Ropelay
PB20TA3QC3QC	18.62mm	500 kcmil Compact
PB10SS2W	19.05mm	250 kcmil Ropelay
PB10SS2W3S	26.42mm	250 kcmil Ropelay
PB10SS3S4M	19.02mm	500 kcmil Ropelay
PB20TA2W3S	26.42mm	250 kcmil Ropelay
PB50PC3S2W	19.05mm	500 kcmil Ropelay
PB50PC5A2W	19.05mm	1000 kcmil Ropelay
PB50SS5A2W	19.05mm	1000 kcmil Ropelay
PB10SS3B3S	26.42mm	300 kcmil Ropelay
PB10SS3Q	20.65mm	500 kcmil Concentric
PB10SS3S3Q	20.65mm	500 kcmil Ropelay
PB20TA3Q3Q	20.65mm	500 kcmil Concentric
PB60TA3Q4Y	29.26mm	500 kcmil Concentric
PB60TA4Y3Q	20.65mm	1000 kcmil Concentric
PB63TA6H3Q	20.65mm	2000 kcmil Concentric
PB80PG5T3Q	20.65mm	1500 kcmil Concentric
PB10SS3S3F	22.35mm	500 kcmil Ropelay
PB10SS4R	22.4mm	1100/#24 Ropelay
PB20TA4R4R	22.4mm	1100/#24 Ropelay
PB10SS3S4T	24.94mm	500 kcmil Ropelay
PB31TA4T4T	24.94mm	1325/#24 Ropelay

Catalog Number	Conductor 2 Outer Diameter, Nominal	Conductor 1
PB50SS4L4T	24.94mm	750 kcmil Concentric
PB10SS4L	25.35mm	750 kcmil Concentric
PB50SS4L3S	26.42mm	750 kcmil Concentric
PB80PA5T4L	25.35mm	1500 kcmil Concentric
PB10SS3S	26.42mm	500 kcmil Ropelay
PB10SS3S4X	27.18mm	500 kcmil Ropelay
PB20TA3S3S	26.42mm	500 kcmil Ropelay
PB50PC3S5A	33.78mm	500 kcmil Ropelay
PB50SS3S4N	29.34mm	500 kcmil Ropelay
PB50SS3S4Y	29.26mm	500 kcmil Ropelay
PB50SS3S5A	33.78mm	500 kcmil Ropelay
PB60TA4N3S	26.42mm	750 kcmil Ropelay
PB60TA4X4X	27.18mm	1600/#24 Ropelay
PB50SS4Y	29.26mm	1000 kcmil Concentric
PB50SS4N	29.34mm	750 kcmil Ropelay
PB50PC5A5A	33.78mm	1000 kcmil Ropelay
PB50SS5A	33.78mm	1000 kcmil Ropelay
PB53SS6H	40.94mm	2000 kcmil Concentric

ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a PB10GR162G becomes XLPB10GR162G). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, PB90 becomes XLPB90).

A gap between conductors may be required. See mold tag for more information.

XXXX-XX-XX-XX-L-M-W		
XXXX	Price Key	
XX	Mold Family	
XX	Conductor Code 1	
XX	Conductor Code 2	
L*	Split Crucible	Crucible section is split on molds designed with horizontal opening for easier cleaning
M*	Mold Only	
W*	Wear Plates	Reduce mechanical abrasion of molds at cable entry points

* Empty if none

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER