

SOCKET STRIP, SCHUKO



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.

CERTIFICATIONS



VLASTNOSTI

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

SPECIFIKACE

Table 1/2

Katalogové číslo	Product Type	Typ zásuvky	Socket Quantity	Switched Outlets	Barva	Napětí střídavé
60110-200	Socket Strip	SCHUKO	3	No	Grey	230V
60110-201	Socket Strip	SCHUKO	4	No	Grey	230V
60110-202	Socket Strip	SCHUKO	9	No	Grey	230V

Katalogové číslo	ProductType	Typ zásuvky	Socket Quantity	Switched Outlets	Barva	Napětí střídavé
60110-203	Socket Strip	SCHUKO	12	No	Grey	230V
60110-204	Socket Strip	SCHUKO	15	No	Grey	230V
60110-205	Socket Strip	SCHUKO	19	No	Grey	230V
60110-206	Socket Strip	SCHUKO	8	Yes	Grey	230V
60110-207	Socket Strip	SCHUKO	12	Yes	Grey	230V
60110-208	Socket Strip	SCHUKO	15	Yes	Grey	230V
60110-209	Socket Strip	SCHUKO	19	Yes	Grey	230V
60110-210	Socket Strip	SCHUKO	8	No	Grey	230V
60110-211	Socket Strip	SCHUKO	9	No	Grey	230V
60110-212	Socket Strip	SCHUKO	6	No	Grey	230V
60110-214	Socket Strip	SCHUKO	7	No	Grey	230V
60110-216	Socket Strip	SCHUKO	6	No	Grey	230V
60110-217	Socket Strip	SCHUKO	6	No	Grey	230V
60110-266	Socket Strip	SCHUKO	6	No	Grey	230V

Table 2/2						
Katalogové číslo	Function	Length	Hloubka	Povrchová úprava	Materiál	Množství v balení
60110-200		184mm	44mm	Anodized	Aluminum, Polyamide	1
60110-201		210mm	44mm	Anodized	Aluminum, Polyamide	1
60110-202		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-203		947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-204		1202mm	44mm	Anodized	Aluminum, Polyamide	1
60110-205		1753mm	44mm	Anodized	Aluminum, Polyamide	1
60110-206		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-207		947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-208		1202mm	44mm	Anodized	Aluminum, Polyamide	1
60110-209		1753mm	44mm	Anodized	Aluminum, Polyamide	1

Katalogové číslo	Function	Length	Hloubka	Povrchová úprava	Materiál	Množství v balení
60110-210	Transient Protection	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-211	Transient Protection	947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-212	Overcurrent Protection	438.5mm	75mm	Anodized	Aluminum, Polyamide	1
60110-214	Mains Suppression Filter	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-216	Fault Current Protection	438.5mm	88mm	Anodized	Aluminum, Polyamide	1
60110-217	Fault Current Protection, Overcurrent Protection	438.5mm	88mm	Anodized	Aluminum, Polyamide	1
60110-266	Transient Protection, Mains Suppression Filter	438.5mm	44mm	Anodized	Aluminum, Polyamide	1

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER