

## PROSKLENÉ DVERE PRO EX PROSTREDÍ, EXWK

Hazardous Location Window Kits are designed to be used on Increased Safety (Ex e) enclosures in ATEX or IECEx Zone 1 or 2 hazardous areas. These window kits ensure a dust-, oil-, and water-tight seal. Designed for use as viewing windows, these window kits are ideal for visibility of internal enclosure components. The windows are easily installed by making a cutout in the enclosure and attaching the window and frame with included mounting hardware.

### PRŮMYSLOVÉ NORMY

UL 508A Component Recognized; Type 4, 4X, 12, 3R; File No. E61997

IECEx and ATEX Approvals

Suitable for use on increased safety enclosures for ZONE 1 or ZONE 2 assemblies

ATEX Directive 94/9/EC

ATEX

Sira 13ATEX3315U

Ex e IIC Gb

Ex tb IIIC Db IP 66

IECEx

IECEx SIR 13.0123U

cUR Component Recognized per CSA C22.2 No. 94; Type 4, 4X, 12,

3R; File No. E61997

NEMA/EEMAC 4, 4X, 12, 13

IEC 60529, IP66



### VLASTNOSTI

Secure sealing with silicon gasket to protect against water and dust ingress in high-temperature applications

Maintain visual on components through .25-in. (6-mm) tempered safety glass

Easy installation in enclosure cutouts with window frame hardware

## SPECIFIKACE

**Povrchová úprava:** Leštěná  
**Materiál:** Nerezová ocel 316L

Table 1/1

| Katalogové číslo | Tloušťka | Cutout Size | Rychlé odeslání |
|------------------|----------|-------------|-----------------|
| EXWK53SS6        | 1.98mm   | 170 x 119mm | Ne              |
| EXWK138SS6       | 1.98mm   | 373 x 246mm | Ne              |
| EXWK1711SS6      | 1.98mm   | 475 x 322mm | Ne              |
| EXWK2315SS6      | 1.98mm   | 627 x 424mm | Ne              |
| EXWK2919SS6      | 1.98mm   | 780 x 526mm | Ne              |
| EXWK711SS6       | 1.98mm   | 221 x 322mm | Ne              |
| EXWK715SS6       | 1.98mm   | 424 x 221mm | Ne              |
| EXWK720SS6       | 1.98mm   | 221 x 551mm | Ne              |
| EXWK724SS6       | 1.98mm   | 221 x 653mm | Ne              |
| EXWK729SS6       | 1.98mm   | 221 x 780mm | Ne              |
| EXWK95SS6        | 1.98mm   | 272 x 183mm | Ne              |

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**