

EUROPACPRO 19" SUBRACK KIT FOR BACKPLANE, SLIDE RAIL, RETROFIT SHIELDING



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFICATIONS



FEATURES

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

SPECIFICATIONS

Table 1/3

Catalog Number	For Mounting	Board Depth	EMC Gasket Type	EMC Shielding	Rack Width	Handle Included
24553-132	Backplane	160 mm, 220 mm	Stainless Steel	No	84 HP	No
24553-133	Backplane	160 mm, 220 mm, 280 mm	Stainless Steel	No	84 HP	No

Catalog Number	ForMounting	Board Depth	EMC Gasket Type	EMC Shielding	Rack Width	Handle Included
24553-134	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel	No	84 HP	No
24553-432	Backplane	160 mm, 220 mm	Stainless Steel	No	84 HP	No
24553-433	Backplane	160 mm, 220 mm, 280 mm	Stainless Steel	No	84 HP	No
24553-434	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel	No	84 HP	No

Table 2/3						
Catalog Number	Package Quantity	Product Type	Rack Height	Complies With	Mounting	Depth
24553-132	1	Subrack/Chassis	3 U	IEC 60297-3-103	Rack	235 mm
24553-133	1	Subrack/Chassis	3 U	IEC 60297-3-103	Rack	295 mm
24553-134	1	Subrack/Chassis	3 U	IEC 60297-3-103	Rack	355 mm
24553-432	1	Subrack/Chassis	6 U	IEC 60297-3-103	Rack	235 mm
24553-433	1	Subrack/Chassis	6 U	IEC 60297-3-103	Rack	295 mm
24553-434	1	Subrack/Chassis	6 U	IEC 60297-3-103	Rack	355 mm

Table 3/3	
Catalog Number	Static Load
24553-132	11 kgf
24553-133	11 kgf
24553-134	11 kgf
24553-432	11 kgf
24553-433	11 kgf
24553-434	11 kgf

ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER