

EUROPACPRO 19" SUBRACK KIT FOR BACKPLANE, SLIDE RAIL, RETROFIT SHIELDING



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFICATIONS



MERKMALE

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

SPEZIFIKATIONEN

Table 1/3

Katalognummer	For Mounting	Board Depth	EMC Gasket Type	EMC Shielding	Rack Width	Handle Included
24553-132	Backplane	160 mm, 220 mm	Edelstahl	Nein	84 HP	Nein
24553-133	Backplane	160 mm, 220 mm, 280 mm	Edelstahl	Nein	84 HP	Nein

Katalognummer	ForMounting	Board Depth	EMC Gasket Type	EMC Shielding	Rack Width	Handle Included
24553-134	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl	Nein	84 HP	Nein
24553-432	Backplane	160 mm, 220 mm	Edelstahl	Nein	84 HP	Nein
24553-433	Backplane	160 mm, 220 mm, 280 mm	Edelstahl	Nein	84 HP	Nein
24553-434	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Edelstahl	Nein	84 HP	Nein

Table 2/3						
Katalognummer	Package Quantity	Product Type	Rack Height	Konform mit	Montage	Tiefe
24553-132	1	Subrack/Chassis	3 U	IEC 60297-3-103	Rack	235 mm
24553-133	1	Subrack/Chassis	3 U	IEC 60297-3-103	Rack	295 mm
24553-134	1	Subrack/Chassis	3 U	IEC 60297-3-103	Rack	355 mm
24553-432	1	Subrack/Chassis	6 U	IEC 60297-3-103	Rack	235 mm
24553-433	1	Subrack/Chassis	6 U	IEC 60297-3-103	Rack	295 mm
24553-434	1	Subrack/Chassis	6 U	IEC 60297-3-103	Rack	355 mm

Table 3/3	
Katalognummer	Statische Last
24553-132	11 kgf
24553-133	11 kgf
24553-134	11 kgf
24553-432	11 kgf
24553-433	11 kgf
24553-434	11 kgf

ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER