


FRONT PANEL, FLAT, REFROFIT SHIELDING, D-SUB CUTOUTS



Flat front panel with cutout for D-Sub connectors. Shieldable for stainless steel EMC gasket.

CERTIFICATIONS



MERKMALE

For stainless steel EMC gasket

Aluminum, 2.5 mm, front anodized, conductive

SPEZIFIKATIONEN

Table 1/3						
Katalognum mer	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30118-348	Edelstahl	Nein	Anodized	Conductive	No (Retrofittable)	4 HP
30118-349	Edelstahl	Nein	Anodized	Conductive	No (Retrofittable)	4 HP

Katalognummer	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30118-350	Edelstahl	Nein	Anodized	Conductive	No (Retrofittable)	4 HP
30118-351	Edelstahl	Nein	Anodized	Conductive	No (Retrofittable)	4 HP
30118-352	Edelstahl	Nein	Anodized	Conductive	No (Retrofittable)	4 HP
30118-353	Edelstahl	Nein	Anodized	Conductive	No (Retrofittable)	4 HP
30118-354	Edelstahl	Nein	Anodized	Conductive	No (Retrofittable)	4 HP

Table 2/3						
Katalognummer	Package Quantity	Höhe	Product Type	Typ	Rack Height	Breite
30118-348	5	128.4 mm	Frontplatte	Front Panel without Handle	3 U	20 mm
30118-349	5	128.4 mm	Frontplatte	Front Panel without Handle	3 U	20 mm
30118-350	5	128.4 mm	Frontplatte	Front Panel without Handle	3 U	20 mm
30118-351	5	128.4 mm	Frontplatte	Front Panel without Handle	3 U	20 mm
30118-352	5	128.4 mm	Frontplatte	Front Panel without Handle	3 U	20 mm
30118-353	5	128.4 mm	Frontplatte	Front Panel without Handle	3 U	20 mm
30118-354	5	128.4 mm	Frontplatte	Front Panel without Handle	3 U	20 mm

Table 3/3			
Katalognummer	Konform mit	Montage	Material
30118-348	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30118-349	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30118-350	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30118-351	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30118-352	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium

Katalognummer	Konform mit	Montage	Material
30118-353	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium
30118-354	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminium

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order stainless steel EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER