


ASSEMBLY PARTS FOR RUGGED COMPONENTS



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

CERTIFICATIONS



MERKMALE

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

SPEZIFIKATIONEN

Table 1/2						
Katalognummer	Gewindegröße	Package Quantity	Product Type	Product Family	Kompatibel mit	Typ
24566-105	M4	100	Assembly Kit	EuropacPRO	Baugruppenträger	Countersunk Screw
24566-104	M4	100	Assembly Kit	EuropacPRO	Baugruppenträger	Panhead Screw
24566-103	M4	100	Assembly Kit	EuropacPRO	Baugruppenträger	Panhead Screw
24566-106	M4	100	Assembly Kit	EuropacPRO	Baugruppenträger	Countersunk Screw
24566-101	M4	100	Assembly Kit	EuropacPRO	Baugruppenträger	Countersunk Screw
24566-102	M4	100	Assembly Kit	EuropacPRO	Baugruppenträger	Panhead Screw

Katalognummer	Gewindegröße	Package Quantity	ProductType	Product Family	Kompatibel mit	Typ
24566-100	M4	100	Assembly Kit	EuropacPRO	Baugruppenträger	Countersunk Screw
24560-140		100	Assembly Kit	EuropacPRO	Baugruppenträger	Square Nut

Table 2/2		
Katalognummer	Material	Länge
24566-105	Edelstahl	7 mm
24566-104	Edelstahl	8 mm
24566-103	Edelstahl	10 mm
24566-106	Edelstahl	10 mm
24566-101	Edelstahl	14 mm
24566-102	Edelstahl	14 mm
24566-100	Edelstahl	18 mm
24560-140	Edelstahl	

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER