

19" ASSEMBLY KIT M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CERTIFICATIONS



FEATURES

- Assembly kits for assembly of 19" components into a cabinet
- For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFICATIONS

Table 1/2						
Catalog Number	Type	Accessory Type	Product Type	Works With	Package Quantity	Finish
21120-196	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	4	Zinc Plated
21120-213	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	4	Zinc Plated

Catalog Number	Type	Accessory Type	ProductType	Works With	Package Quantity	Finish
21100-435	Mounting Kit	Mounting hardware	Assembly Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	8	Zinc Plated
21120-199	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	100	Zinc Plated
21120-197	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	32	Zinc Plated
21120-198	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	50	Zinc Plated
21101-809	Mounting Kit	Mounting hardware	Assembly Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	50	Zinc Plated
21101-810	Mounting Kit	Mounting hardware	Assembly Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	100	Zinc Plated
21120-215	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	32	Zinc Plated
21120-214	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	50	Zinc Plated
21120-216	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	100	Zinc Plated

Table 2/2

Catalog Number	Material	Length	Thread Size	Certifications
21120-196	Steel	16mm	M6	
21120-213	Steel		M6	
21100-435	Steel, ABS		M6	RoHS
21120-199	Steel	13mm	M6	
21120-197	Steel	16mm	M6	
21120-198	Steel	16mm	M6	
21101-809	Steel, ABS		M6	RoHS
21101-810	Steel, ABS		M6	RoHS
21120-215	Steel		M6	
21120-214	Steel		M6	
21120-216	Steel		M6	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER