

## FRONT PANEL, UNSHIELDED, WITH FASTENER PIN



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

### CERTIFICATIONS



### MERKMALE

Enable grounding of the front area (protection class 1)

### SPEZIFIKATIONEN

Table 1/3

| Katalognummer | Treated Edges | Front Finish | Rear Finish | EMC Shielding | Rack Width | Package Quantity |
|---------------|---------------|--------------|-------------|---------------|------------|------------------|
| 20119-159     | Nein          | Anodized     | Conductive  | Nein          | 7 HP       | 1                |
| 20119-160     | Nein          | Anodized     | Conductive  | Nein          | 14 HP      | 1                |
| 20119-161     | Nein          | Anodized     | Conductive  | Nein          | 21 HP      | 1                |
| 20119-162     | Nein          | Anodized     | Conductive  | Nein          | 28 HP      | 1                |
| 20119-163     | Nein          | Anodized     | Anodized    | Nein          | 42 HP      | 1                |

Table 2/3

| Katalognummer | Höhe | Product Type | Typ | Rack Height | Breite | Konform mit |
|---------------|------|--------------|-----|-------------|--------|-------------|
|---------------|------|--------------|-----|-------------|--------|-------------|

|           |          |             |                            |     |          |                                 |
|-----------|----------|-------------|----------------------------|-----|----------|---------------------------------|
| 20119-159 | 128.4 mm | Frontplatte | Front Panel without Handle | 3 U | 35.2 mm  | IEC 60297-3-101, IEEE 1101.1/10 |
| 20119-160 | 128.4 mm | Frontplatte | Front Panel without Handle | 3 U | 70.8 mm  | IEC 60297-3-101, IEEE 1101.1/10 |
| 20119-161 | 128.4 mm | Frontplatte | Front Panel without Handle | 3 U | 106.3 mm | IEC 60297-3-101, IEEE 1101.1/10 |
| 20119-162 | 128.4 mm | Frontplatte | Front Panel without Handle | 3 U | 141.9 mm | IEC 60297-3-101, IEEE 1101.1/10 |
| 20119-163 | 128.4 mm | Frontplatte | Front Panel without Handle | 3 U | 213 mm   | IEC 60297-3-101, IEEE 1101.1/10 |

Table 3/3

| Katalognummer | Montage        | Material  |
|---------------|----------------|-----------|
| 20119-159     | Screw-on Front | Aluminium |
| 20119-160     | Screw-on Front | Aluminium |
| 20119-161     | Screw-on Front | Aluminium |
| 20119-162     | Screw-on Front | Aluminium |
| 20119-163     | Screw-on Front | Aluminium |

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter [www.nVent.com](http://www.nVent.com) sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**