

SOCKET STRIP, SCHUKO



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.

CERTIFICATIONS



FEATURES

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-200	Socket Strip	SCHUKO	3	No	Grey	230V
60110-201	Socket Strip	SCHUKO	4	No	Grey	230V
60110-202	Socket Strip	SCHUKO	9	No	Grey	230V

Catalog Number	ProductType	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-203	Socket Strip	SCHUKO	12	No	Grey	230V
60110-204	Socket Strip	SCHUKO	15	No	Grey	230V
60110-205	Socket Strip	SCHUKO	19	No	Grey	230V
60110-206	Socket Strip	SCHUKO	8	Yes	Grey	230V
60110-207	Socket Strip	SCHUKO	12	Yes	Grey	230V
60110-208	Socket Strip	SCHUKO	15	Yes	Grey	230V
60110-209	Socket Strip	SCHUKO	19	Yes	Grey	230V
60110-210	Socket Strip	SCHUKO	8	No	Grey	230V
60110-211	Socket Strip	SCHUKO	9	No	Grey	230V
60110-212	Socket Strip	SCHUKO	6	No	Grey	230V
60110-214	Socket Strip	SCHUKO	7	No	Grey	230V
60110-216	Socket Strip	SCHUKO	6	No	Grey	230V
60110-217	Socket Strip	SCHUKO	6	No	Grey	230V
60110-266	Socket Strip	SCHUKO	6	No	Grey	230V

Table 2/2						
Catalog Number	Function	Length	Depth	Finish	Material	Package Quantity
60110-200		184mm	44mm	Anodized	Aluminum, Polyamide	1
60110-201		210mm	44mm	Anodized	Aluminum, Polyamide	1
60110-202		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-203		947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-204		1202mm	44mm	Anodized	Aluminum, Polyamide	1
60110-205		1753mm	44mm	Anodized	Aluminum, Polyamide	1
60110-206		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-207		947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-208		1202mm	44mm	Anodized	Aluminum, Polyamide	1
60110-209		1753mm	44mm	Anodized	Aluminum, Polyamide	1

Catalog Number	Function	Length	Depth	Finish	Material	Package Quantity
60110-210	Transient Protection	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-211	Transient Protection	947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-212	Overcurrent Protection	438.5mm	75mm	Anodized	Aluminum, Polyamide	1
60110-214	Mains Suppression Filter	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-216	Fault Current Protection	438.5mm	88mm	Anodized	Aluminum, Polyamide	1
60110-217	Fault Current Protection, Overcurrent Protection	438.5mm	88mm	Anodized	Aluminum, Polyamide	1
60110-266	Transient Protection, Mains Suppression Filter	438.5mm	44mm	Anodized	Aluminum, Polyamide	1

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER