

VARISTAR NET PLUS CABINET



Basic rack to support cabling and networking equipment.
Cooling via convection or top cover fans.

CERTIFICATIONS



FEATURES

Available as side by side or standalone rack

Cabling cabinet with two 19"planes and base/plinth

Type of protection IP 20

SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
10130-072	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-073	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-074	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-075	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-076	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-077	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-078	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey

Catalog Number	ProductType	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
10130-079	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-080	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-081	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-082	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-083	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-084	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-085	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-086	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-087	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-088	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-089	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-090	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-091	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-092	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-093	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-094	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-095	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-096	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-097	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-098	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-099	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-100	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-101	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-102	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-103	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-104	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-105	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-106	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-107	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-108	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-109	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-110	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-111	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-112	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey

Catalog Number	ProductType	Frame Material	Cladding Material	Frame Color	Frame Color Code	Cladding Color
10130-113	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-114	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-115	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-116	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-117	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-118	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey
10130-119	Rack	Steel	Steel	Black Grey	RAL 7021	Light Grey

Table 2/3						
Catalog Number	Cladding Color Code	Static Load	Rack Height	Height	Material	Finish
10130-072	RAL 7035	800kgf	24U	1200mm	Steel	Powder Coated
10130-073	RAL 7035	800kgf	24U	1200mm	Steel	Powder Coated
10130-074	RAL 7035	800kgf	24U	1200mm	Steel	Powder Coated
10130-075	RAL 7035	800kgf	24U	1200mm	Steel	Powder Coated
10130-076	RAL 7035	800kgf	24U	1200mm	Steel	Powder Coated
10130-077	RAL 7035	800kgf	24U	1200mm	Steel	Powder Coated
10130-078	RAL 7035	800kgf	24U	1200mm	Steel	Powder Coated
10130-079	RAL 7035	800kgf	24U	1200mm	Steel	Powder Coated
10130-080	RAL 7035	400kgf	24U	1200mm	Steel	Powder Coated
10130-081	RAL 7035	400kgf	24U	1200mm	Steel	Powder Coated
10130-082	RAL 7035	400kgf	24U	1200mm	Steel	Powder Coated
10130-083	RAL 7035	400kgf	24U	1200mm	Steel	Powder Coated
10130-084	RAL 7035	400kgf	24U	1200mm	Steel	Powder Coated
10130-085	RAL 7035	400kgf	24U	1200mm	Steel	Powder Coated
10130-086	RAL 7035	400kgf	24U	1200mm	Steel	Powder Coated
10130-087	RAL 7035	400kgf	24U	1200mm	Steel	Powder Coated
10130-088	RAL 7035	800kgf	42U	2000mm	Steel	Powder Coated
10130-089	RAL 7035	800kgf	42U	2000mm	Steel	Powder Coated
10130-090	RAL 7035	800kgf	42U	2000mm	Steel	Powder Coated
10130-091	RAL 7035	800kgf	42U	2000mm	Steel	Powder Coated
10130-092	RAL 7035	800kgf	42U	2000mm	Steel	Powder Coated
10130-093	RAL 7035	800kgf	42U	2000mm	Steel	Powder Coated
10130-094	RAL 7035	800kgf	42U	2000mm	Steel	Powder Coated
10130-095	RAL 7035	800kgf	42U	2000mm	Steel	Powder Coated

Catalog Number	Cladding Color Code	Static Load	Rack Height	Height	Material	Finish
10130-096	RAL 7035	400kgf	42U	2000mm	Steel	Powder Coated
10130-097	RAL 7035	400kgf	42U	2000mm	Steel	Powder Coated
10130-098	RAL 7035	400kgf	42U	2000mm	Steel	Powder Coated
10130-099	RAL 7035	400kgf	42U	2000mm	Steel	Powder Coated
10130-100	RAL 7035	400kgf	42U	2000mm	Steel	Powder Coated
10130-101	RAL 7035	400kgf	42U	2000mm	Steel	Powder Coated
10130-102	RAL 7035	400kgf	42U	2000mm	Steel	Powder Coated
10130-103	RAL 7035	400kgf	42U	2000mm	Steel	Powder Coated
10130-104	RAL 7035	800kgf	47U	2200mm	Steel	Powder Coated
10130-105	RAL 7035	800kgf	47U	2200mm	Steel	Powder Coated
10130-106	RAL 7035	800kgf	47U	2200mm	Steel	Powder Coated
10130-107	RAL 7035	800kgf	47U	2200mm	Steel	Powder Coated
10130-108	RAL 7035	800kgf	47U	2200mm	Steel	Powder Coated
10130-109	RAL 7035	800kgf	47U	2200mm	Steel	Powder Coated
10130-110	RAL 7035	800kgf	47U	2200mm	Steel	Powder Coated
10130-111	RAL 7035	800kgf	47U	2200mm	Steel	Powder Coated
10130-112	RAL 7035	400kgf	47U	2200mm	Steel	Powder Coated
10130-113	RAL 7035	400kgf	47U	2200mm	Steel	Powder Coated
10130-114	RAL 7035	400kgf	47U	2200mm	Steel	Powder Coated
10130-115	RAL 7035	400kgf	47U	2200mm	Steel	Powder Coated
10130-116	RAL 7035	400kgf	47U	2200mm	Steel	Powder Coated
10130-117	RAL 7035	400kgf	47U	2200mm	Steel	Powder Coated
10130-118	RAL 7035	400kgf	47U	2200mm	Steel	Powder Coated
10130-119	RAL 7035	400kgf	47U	2200mm	Steel	Powder Coated

Table 3/3			
Catalog Number	Package Quantity	Width	Depth
10130-072	1	600mm	600mm
10130-073	1	600mm	600mm
10130-074	1	600mm	800mm
10130-075	1	600mm	800mm
10130-076	1	600mm	900mm
10130-077	1	600mm	900mm
10130-078	1	600mm	1000mm
10130-079	1	600mm	1000mm

Catalog Number	Package Quantity	Width	Depth
10130-080	1	800mm	600mm
10130-081	1	800mm	600mm
10130-082	1	800mm	800mm
10130-083	1	800mm	800mm
10130-084	1	800mm	900mm
10130-085	1	800mm	900mm
10130-086	1	800mm	1000mm
10130-087	1	800mm	1000mm
10130-088	1	600mm	600mm
10130-089	1	600mm	600mm
10130-090	1	600mm	800mm
10130-091	1	600mm	800mm
10130-092	1	600mm	900mm
10130-093	1	600mm	900mm
10130-094	1	600mm	1000mm
10130-095	1	600mm	1000mm
10130-096	1	800mm	600mm
10130-097	1	800mm	600mm
10130-098	1	800mm	800mm
10130-099	1	800mm	800mm
10130-100	1	800mm	900mm
10130-101	1	800mm	900mm
10130-102	1	800mm	1000mm
10130-103	1	800mm	1000mm
10130-104	1	600mm	600mm
10130-105	1	600mm	600mm
10130-106	1	600mm	800mm
10130-107	1	600mm	800mm
10130-108	1	600mm	900mm
10130-109	1	600mm	900mm
10130-110	1	600mm	1000mm
10130-111	1	600mm	1000mm
10130-112	1	800mm	600mm
10130-113	1	800mm	600mm
10130-114	1	800mm	800mm

Catalog Number	Package Quantity	Width	Depth
10130-115	1	800mm	800mm
10130-116	1	800mm	900mm
10130-117	1	800mm	900mm
10130-118	1	800mm	1000mm
10130-119	1	800mm	1000mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER