

VARISTAR CP SWING FRAME FOR 800 MM WIDTH

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

FEATURES

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

SPECIFICATIONS

Table 1/2

Catalog Number	Height	Product Type	Product Family	Rack Height	Width	Color
21630-669	1200 mm	Cabinet/Rack Frame	Varistar CP	24 U	800 mm	Black Grey
21630-680	1200 mm	Cabinet/Rack Frame	Varistar CP	24 U	800 mm	Black Grey
21630-671	1400 mm	Cabinet/Rack Frame	Varistar CP	29 U	800 mm	Black Grey
21630-681	1400 mm	Cabinet/Rack Frame	Varistar CP	29 U	800 mm	Black Grey
21630-673	1600 mm	Cabinet/Rack Frame	Varistar CP	33 U	800 mm	Black Grey
21630-682	1600 mm	Cabinet/Rack Frame	Varistar CP	33 U	800 mm	Black Grey
21630-675	1800 mm	Cabinet/Rack Frame	Varistar CP	38 U	800 mm	Black Grey
21630-683	1800 mm	Cabinet/Rack Frame	Varistar CP	38 U	800 mm	Black Grey
21630-677	2000 mm	Cabinet/Rack Frame	Varistar CP	42 U	800 mm	Black Grey

Catalog Number	Height	ProductType	Product Family	Rack Height	Width	Color
21630-684	2000 mm	Cabinet/Rack Frame	Varistar CP	42 U	800 mm	Black Grey
21630-679	2200 mm	Cabinet/Rack Frame	Varistar CP	47 U	800 mm	Black Grey
21630-685	2200 mm	Cabinet/Rack Frame	Varistar CP	47 U	800 mm	Black Grey

Table 2/2			
Catalog Number	Material	Color Code	Protection Rating
21630-669	Steel	RAL 7021	IP20
21630-680	Steel	RAL 7021	IP20
21630-671	Steel	RAL 7021	IP20
21630-681	Steel	RAL 7021	IP20
21630-673	Steel	RAL 7021	IP20
21630-682	Steel	RAL 7021	IP20
21630-675	Steel	RAL 7021	IP20
21630-683	Steel	RAL 7021	IP20
21630-677	Steel	RAL 7021	IP20
21630-684	Steel	RAL 7021	IP20
21630-679	Steel	RAL 7021	IP20
21630-685	Steel	RAL 7021	IP20

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER