



Flat front panel with cutout for D-Sub connectors. Unshielded version.

## CERTIFICATIONS



## FEATURES

Non-shielded version

Aluminum, 2.5 mm, front anodized, rear conductive

## SPECIFICATIONS

Table 1/3						
Catalog Number	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
30118-341	No	Anodized	Conductive	No	4 HP	5
30118-342	No	Anodized	Conductive	No	4 HP	5
30118-343	No	Anodized	Conductive	No	4 HP	5
30118-344	No	Anodized	Conductive	No	4 HP	5

Catalog Number	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
30118-345	No	Anodized	Conductive	No	4 HP	5
30118-346	No	Anodized	Conductive	No	4 HP	5
30118-347	No	Anodized	Conductive	No	4 HP	5

Table 2/3						
Catalog Number	Height	Product Type	Type	Rack Height	Width	Complies With
30118-341	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-342	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-343	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-344	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-345	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-346	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-347	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10

Table 3/3		
Catalog Number	Mounting	Material
30118-341	Screw-on Front	Aluminum
30118-342	Screw-on Front	Aluminum
30118-343	Screw-on Front	Aluminum
30118-344	Screw-on Front	Aluminum
30118-345	Screw-on Front	Aluminum
30118-346	Screw-on Front	Aluminum
30118-347	Screw-on Front	Aluminum

## ADDITIONAL PRODUCT DETAILS

---

Delivery is in standard pack multiples. Pricing is per individual item.

Please order fixing material (sleeves, collar screws) separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**