

SOCKET STRIP, IEC, 3-PHASE



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 and C19 outlets with 3 phase input.

CERTIFICATIONS



FEATURES

Socket strips with IEC sockets in accordance with IEC 60320

Vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Connecting cable 2 m

Mounting height 1 U

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-283	Socket Strip	IEC C13	18	No	Grey, Black, Red	400V
60110-284	Socket Strip	IEC C13, IEC C19	24	No	Grey, Black, Red	400V
60110-285	Socket Strip	IEC C13, IEC C19	30	No	Grey, Black, Red	400V

Table 2/2

Catalog Number	Height	Length	Depth	Material	Finish	Package Quantity
60110-283	44mm	947.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-284	44mm	947.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-285	44mm	1753mm	44mm	Aluminum, Polyamide	Anodized	1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY** **ERICO** **HOFFMAN** **RAYCHEM** **SCHROFF**
TRACER