

FRONT PANEL, FLAT, REFROFIT SHIELDING, D-SUB CUTOUTS



Flat front panel with cutout for D-Sub connectors. Shieldable for stainless steel EMC gasket.

CERTIFICATIONS



FEATURES

For stainless steel EMC gasket

Aluminum, 2.5 mm, front anodized, conductive

SPECIFICATIONS

Table 1/3

Catalog Number	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30118-348	Stainless Steel	No	Anodized	Conductive	No (Retrofittable)	4 HP
30118-349	Stainless Steel	No	Anodized	Conductive	No (Retrofittable)	4 HP

Catalog Number	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30118-350	Stainless Steel	No	Anodized	Conductive	No (Retrofittable)	4 HP
30118-351	Stainless Steel	No	Anodized	Conductive	No (Retrofittable)	4 HP
30118-352	Stainless Steel	No	Anodized	Conductive	No (Retrofittable)	4 HP
30118-353	Stainless Steel	No	Anodized	Conductive	No (Retrofittable)	4 HP
30118-354	Stainless Steel	No	Anodized	Conductive	No (Retrofittable)	4 HP

Table 2/3						
Catalog Number	Package Quantity	Height	Product Type	Type	Rack Height	Width
30118-348	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30118-349	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30118-350	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30118-351	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30118-352	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30118-353	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30118-354	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm

Table 3/3			
Catalog Number	Complies With	Mounting	Material
30118-348	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30118-349	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30118-350	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30118-351	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30118-352	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum

Catalog Number	Complies With	Mounting	Material
30118-353	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30118-354	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order stainless steel EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER