


## FRONT HANDLE ONE-PIECE, WIDTH 12.2 MM



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

### CERTIFICATIONS



### FEATURES

Static load-carrying capacity 30 kg/pair

Bolted from rear

### SPECIFICATIONS

Table 1/2

| Catalog Number | Handle Type   | Package Quantity | Type             | Product Type | Product Family | Works With |
|----------------|---------------|------------------|------------------|--------------|----------------|------------|
| 10501-116      | Straight      | 1                | Straight version | Handle       | EuropacPRO     | Subracks   |
| 10501-004      | Straight      | 1                | Straight version | Handle       | EuropacPRO     | Subracks   |
| 10501-020      | Angled Handle | 1                | Angled version   | Handle       | EuropacPRO     | Subracks   |
| 10501-026      | Straight      | 1                | Straight version | Handle       | EuropacPRO     | Subracks   |
| 10501-005      | Straight      | 1                | Straight version | Handle       | EuropacPRO     | Subracks   |
| 10501-006      | Straight      | 1                | Straight version | Handle       | EuropacPRO     | Subracks   |
| 10501-007      | Straight      | 1                | Straight version | Handle       | EuropacPRO     | Subracks   |
| 10501-022      | Angled Handle | 1                | Angled version   | Handle       | EuropacPRO     | Subracks   |

| Catalog Number | Handle Type   | Package Quantity | Type             | ProductType | Product Family | Works With |
|----------------|---------------|------------------|------------------|-------------|----------------|------------|
| 10501-029      | Straight      | 1                | Straight version | Handle      | EuropacPRO     | Subracks   |
| 10501-008      | Straight      | 1                | Straight version | Handle      | EuropacPRO     | Subracks   |
| 10501-016      | Straight      | 1                | Straight version | Handle      | EuropacPRO     | Subracks   |
| 10501-021      | Angled Handle | 1                | Angled version   | Handle      | EuropacPRO     | Subracks   |
| 10501-018      | Straight      | 1                | Straight version | Handle      | EuropacPRO     | Subracks   |
| 10501-025      | Straight      | 1                | Straight version | Handle      | EuropacPRO     | Subracks   |
| 10501-027      | Straight      | 1                | Straight version | Handle      | EuropacPRO     | Subracks   |
| 10501-028      | Straight      | 1                | Straight version | Handle      | EuropacPRO     | Subracks   |

| Table 2/2      |             |        |          |                |         |
|----------------|-------------|--------|----------|----------------|---------|
| Catalog Number | Rack Height | Color  | Material | Accessory Type | Torque  |
| 10501-116      | 1 U         | Silver | Aluminum | Front panel    |         |
| 10501-004      | 2 U         | Silver | Aluminum | Front panel    |         |
| 10501-020      | 3 U         | Silver | Aluminum |                | 2.4 N·m |
| 10501-026      | 3 U         | Black  | Aluminum | Front panel    | 2.4 N·m |
| 10501-005      | 3 U         | Silver | Aluminum |                | 2.4 N·m |
| 10501-006      | 4 U         | Silver | Aluminum | Front panel    |         |
| 10501-007      | 5 U         | Silver | Aluminum | Front panel    |         |
| 10501-022      | 6 U         | Silver | Aluminum |                | 2.4 N·m |
| 10501-029      | 6 U         | Black  | Aluminum | Front panel    | 2.4 N·m |
| 10501-008      | 6 U         | Silver | Aluminum |                | 2.4 N·m |
| 10501-016      | 2 U         | Silver | Aluminum | Front panel    |         |
| 10501-021      | 4 U         | Silver | Aluminum |                | 2.4 N·m |
| 10501-018      | 4 U         | Silver | Aluminum | Front panel    | 2.4 N·m |
| 10501-025      | 2 U         | Black  | Aluminum | Front panel    |         |
| 10501-027      | 4 U         | Black  | Aluminum | Front panel    |         |
| 10501-028      | 5 U         | Black  | Aluminum | Front panel    |         |

## ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**