


CABLE TO GROUND RECEPTACLE OR GROUND PLATE, RA (TO GROUND PLATE), 4/0 GROUND PLATE, 250 KCMIL CONCENTRIC

CATALOG NUMBER

**RAC2V2Q**



nVent ERICO Cadweld graphite molds are designed and engineered for thousands of connection styles and conductor combinations.

CERTIFICATIONS



FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

PRODUCT ATTRIBUTES

Mold Family: RA (To Ground Plate) Mold Family

Conductor Size: 250 kcmil Concentric

Conductor Outer Diameter, Nominal: 14.61mm

Ground Plate/Grounding Receptacle: 4/0 Ground Plate

Mold Split: Vertical

Split Crucible: No

Wear Plates: No

Mold Only: No

Welding Material: 200 or 200PLUSF20, Sold Separately

Handle Clamp: L160, Sold Separately

Price Key: C

Ease of Use: Preferred

## ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).

A gap between conductors may be required. See mold tag for more information.

| XX-X-XX-XX-L-M-W |                                   |                                                                                         |
|------------------|-----------------------------------|-----------------------------------------------------------------------------------------|
| XX               | Mold Family                       |                                                                                         |
| X                | Price Key                         |                                                                                         |
| XX               | Ground Plate/Grounding Receptacle |                                                                                         |
| XX               | Conductor Code                    |                                                                                         |
| L*               | Split Crucible                    | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M*               | Mold Only                         |                                                                                         |
| W*               | Wear Plates                       | Reduce mechanical abrasion of molds at cable entry points                               |

\* Empty if none

| XX-X-XX-XX-XX-XX-L-M-W |                      |                                                                                         |
|------------------------|----------------------|-----------------------------------------------------------------------------------------|
| XX                     | Mold Family          |                                                                                         |
| X                      | Price Key            |                                                                                         |
| XX                     | Mold Family          |                                                                                         |
| XX                     | Ground Rod Type      |                                                                                         |
| XX                     | Conductor Code       |                                                                                         |
| XX                     | Grounding Receptacle |                                                                                         |
| L*                     | Split Crucible       | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M*                     | Mold Only            |                                                                                         |
| W*                     | Wear Plates          | Reduce mechanical abrasion of molds at cable entry points                               |

\* Empty if none

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**