


## SOCKET STRIP, IEC C13



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C13 outlets.

### CERTIFICATIONS



### FEATURES

230 V, 10 A

Horizontal and vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Socket strips with IEC 60320-C13 sockets

Connecting cable 2 m, open end with ferrules

In accordance with IEC 60320

Mounting height 1 U

### SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-290	Socket Strip	IEC C13	8	No	Grey	230V
60110-291	Socket Strip	IEC C13	12	No	Grey	230V
60110-292	Socket Strip	IEC C13	16	No	Grey	230V

Table 2/2

Catalog Number	Length	Depth	Material	Finish	Package Quantity
60110-290	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-291	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-292	608.5mm	44mm	Aluminum, Polyamide	Anodized	1

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)



Our powerful portfolio of brands:  
**nVent.com** **CADDY** **ERICO** **HOFFMAN** **RAYCHEM** **SCHROFF**  
**TRACER**