

VARISTAR CP FRAME



Varistar CP welded frame is available for static load requirements and can be integrated with 19", ETSI or mounting plate. Additionally, castors can be added to the frame if needed.

However, if you require castors for your application, you might want to consider a mobile frame that already includes castors.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Frame Material	Complies With	Product Type	Height	Works With
20630-065	Standard	Steel		Cabinet/Rack Frame	1200mm	Varistar CP
20630-066	Standard	Steel		Cabinet/Rack Frame	1200mm	Varistar CP
20630-067	Standard	Steel		Cabinet/Rack Frame	1200mm	Varistar CP
20630-068	Standard	Steel		Cabinet/Rack Frame	1200mm	Varistar CP
20630-071	Standard	Steel		Cabinet/Rack Frame	1200mm	Varistar CP
20630-072	Standard	Steel		Cabinet/Rack Frame	1200mm	Varistar CP
20630-073	Standard	Steel		Cabinet/Rack Frame	1200mm	Varistar CP

Catalog Number	Type	Frame Material	Complies With	ProductType	Height	Works With
20630-074	Standard	Steel		Cabinet/Rack Frame	1200mm	Varistar CP
20630-075	Standard	Steel		Cabinet/Rack Frame	1400mm	Varistar CP
20630-076	Standard	Steel		Cabinet/Rack Frame	1400mm	Varistar CP
20630-077	Standard	Steel		Cabinet/Rack Frame	1400mm	Varistar CP
20630-078	Standard	Steel		Cabinet/Rack Frame	1400mm	Varistar CP
20630-079	Standard	Steel		Cabinet/Rack Frame	1400mm	Varistar CP
20630-080	Standard	Steel		Cabinet/Rack Frame	1400mm	Varistar CP
20630-081	Standard	Steel		Cabinet/Rack Frame	1400mm	Varistar CP
20630-082	Standard	Steel		Cabinet/Rack Frame	1400mm	Varistar CP
20630-083	Standard	Steel		Cabinet/Rack Frame	1600mm	Varistar CP
20630-084	Standard	Steel		Cabinet/Rack Frame	1600mm	Varistar CP
20630-085	Standard	Steel		Cabinet/Rack Frame	1600mm	Varistar CP
20630-086	Standard	Steel		Cabinet/Rack Frame	1600mm	Varistar CP
20630-087	Standard	Steel		Cabinet/Rack Frame	1600mm	Varistar CP
20630-088	Standard	Steel		Cabinet/Rack Frame	1600mm	Varistar CP
20630-089	Standard	Steel		Cabinet/Rack Frame	1600mm	Varistar CP
20630-090	Standard	Steel		Cabinet/Rack Frame	1600mm	Varistar CP
20630-091	Standard	Steel		Cabinet/Rack Frame	1800mm	Varistar CP
20630-092	Standard	Steel		Cabinet/Rack Frame	1800mm	Varistar CP
20630-093	Standard	Steel		Cabinet/Rack Frame	1800mm	Varistar CP

Catalog Number	Type	Frame Material	Complies With	ProductType	Height	Works With
20630-094	Standard	Steel		Cabinet/Rack Frame	1800mm	Varistar CP
20630-095	Standard	Steel		Cabinet/Rack Frame	1800mm	Varistar CP
20630-096	Standard	Steel		Cabinet/Rack Frame	1800mm	Varistar CP
20630-097	Standard	Steel		Cabinet/Rack Frame	1800mm	Varistar CP
20630-098	Standard	Steel		Cabinet/Rack Frame	1800mm	Varistar CP
20630-099	Standard	Steel		Cabinet/Rack Frame	2000mm	Varistar CP
20630-100	Standard	Steel		Cabinet/Rack Frame	2000mm	Varistar CP
20630-101	Standard	Steel		Cabinet/Rack Frame	2000mm	Varistar CP
20630-102	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm	Varistar CP
20630-103	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm	Varistar CP
20630-104	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm	Varistar CP
20630-105	Standard	Steel		Cabinet/Rack Frame	2000mm	Varistar CP
20630-106	Standard	Steel		Cabinet/Rack Frame	2000mm	Varistar CP
20630-107	Standard	Steel		Cabinet/Rack Frame	2000mm	Varistar CP
20630-108	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm	Varistar CP
20630-109	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm	Varistar CP
20630-110	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2000mm	Varistar CP
20630-111	Standard	Steel		Cabinet/Rack Frame	2200mm	Varistar CP
20630-112	Standard	Steel		Cabinet/Rack Frame	2200mm	Varistar CP
20630-113	Standard	Steel		Cabinet/Rack Frame	2200mm	Varistar CP

Catalog Number	Type	Frame Material	Complies With	ProductType	Height	Works With
20630-114	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm	Varistar CP
20630-115	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm	Varistar CP
20630-116	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm	Varistar CP
20630-117	Standard	Steel		Cabinet/Rack Frame	2200mm	Varistar CP
20630-118	Standard	Steel		Cabinet/Rack Frame	2200mm	Varistar CP
20630-119	Standard	Steel		Cabinet/Rack Frame	2200mm	Varistar CP
20630-120	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm	Varistar CP
20630-121	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm	Varistar CP
20630-122	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2200mm	Varistar CP
20630-123	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm	Varistar CP
20630-124	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm	Varistar CP
20630-125	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm	Varistar CP
20630-126	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm	Varistar CP
20630-127	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm	Varistar CP
20630-128	Standard	Steel	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	2450mm	Varistar CP
20630-261	Standard	Steel		Cabinet/Rack Frame	2000mm	Varistar CP
20630-262	Standard	Steel		Cabinet/Rack Frame	2200mm	Varistar CP

Table 2/3						
Catalog Number	Rack Height	Package Quantity	Material	Color	Color Code	Width
20630-065	24U	1	Steel	Black Grey	RAL 7021	600mm
20630-066	24U	1	Steel	Black Grey	RAL 7021	600mm
20630-067	24U	1	Steel	Black Grey	RAL 7021	600mm

Catalog Number	Rack Height	Package Quantity	Material	Color	Color Code	Width
20630-068	24U	1	Steel	Black Grey	RAL 7021	600mm
20630-071	24U	1	Steel	Black Grey	RAL 7021	800mm
20630-072	24U	1	Steel	Black Grey	RAL 7021	800mm
20630-073	24U	1	Steel	Black Grey	RAL 7021	800mm
20630-074	24U	1	Steel	Black Grey	RAL 7021	800mm
20630-075	29U	1	Steel	Black Grey	RAL 7021	600mm
20630-076	29U	1	Steel	Black Grey	RAL 7021	600mm
20630-077	29U	1	Steel	Black Grey	RAL 7021	600mm
20630-078	29U	1	Steel	Black Grey	RAL 7021	600mm
20630-079	29U	1	Steel	Black Grey	RAL 7021	800mm
20630-080	29U	1	Steel	Black Grey	RAL 7021	800mm
20630-081	29U	1	Steel	Black Grey	RAL 7021	800mm
20630-082	29U	1	Steel	Black Grey	RAL 7021	800mm
20630-083	33U	1	Steel	Black Grey	RAL 7021	600mm
20630-084	33U	1	Steel	Black Grey	RAL 7021	600mm
20630-085	33U	1	Steel	Black Grey	RAL 7021	600mm
20630-086	33U	1	Steel	Black Grey	RAL 7021	600mm
20630-087	33U	1	Steel	Black Grey	RAL 7021	800mm
20630-088	33U	1	Steel	Black Grey	RAL 7021	800mm
20630-089	33U	1	Steel	Black Grey	RAL 7021	800mm
20630-090	33U	1	Steel	Black Grey	RAL 7021	800mm
20630-091	38U	1	Steel	Black Grey	RAL 7021	600mm
20630-092	38U	1	Steel	Black Grey	RAL 7021	600mm
20630-093	38U	1	Steel	Black Grey	RAL 7021	600mm
20630-094	38U	1	Steel	Black Grey	RAL 7021	600mm
20630-095	38U	1	Steel	Black Grey	RAL 7021	800mm
20630-096	38U	1	Steel	Black Grey	RAL 7021	800mm
20630-097	38U	1	Steel	Black Grey	RAL 7021	800mm
20630-098	38U	1	Steel	Black Grey	RAL 7021	800mm
20630-099	42U	1	Steel	Black Grey	RAL 7021	600mm
20630-100	42U	1	Steel	Black Grey	RAL 7021	600mm
20630-101	42U	1	Steel	Black Grey	RAL 7021	600mm
20630-102	42U	1	Steel	Black Grey	RAL 7021	600mm
20630-103	42U	1	Steel	Black Grey	RAL 7021	600mm

Catalog Number	Rack Height	Package Quantity	Material	Color	Color Code	Width
20630-104	42U	1	Steel	Black Grey	RAL 7021	600mm
20630-105	42U	1	Steel	Black Grey	RAL 7021	800mm
20630-106	42U	1	Steel	Black Grey	RAL 7021	800mm
20630-107	42U	1	Steel	Black Grey	RAL 7021	800mm
20630-108	42U	1	Steel	Black Grey	RAL 7021	800mm
20630-109	42U	1	Steel	Black Grey	RAL 7021	800mm
20630-110	42U	1	Steel	Black Grey	RAL 7021	800mm
20630-111	47U	1	Steel	Black Grey	RAL 7021	600mm
20630-112	47U	1	Steel	Black Grey	RAL 7021	600mm
20630-113	47U	1	Steel	Black Grey	RAL 7021	600mm
20630-114	47U	1	Steel	Black Grey	RAL 7021	600mm
20630-115	47U	1	Steel	Black Grey	RAL 7021	600mm
20630-116	47U	1	Steel	Black Grey	RAL 7021	600mm
20630-117	47U	1	Steel	Black Grey	RAL 7021	800mm
20630-118	47U	1	Steel	Black Grey	RAL 7021	800mm
20630-119	47U	1	Steel	Black Grey	RAL 7021	800mm
20630-120	47U	1	Steel	Black Grey	RAL 7021	800mm
20630-121	47U	1	Steel	Black Grey	RAL 7021	800mm
20630-122	47U	1	Steel	Black Grey	RAL 7021	800mm
20630-123	52U	1	Steel	Black Grey	RAL 7021	600mm
20630-124	52U	1	Steel	Black Grey	RAL 7021	600mm
20630-125	52U	1	Steel	Black Grey	RAL 7021	600mm
20630-126	52U	1	Steel	Black Grey	RAL 7021	800mm
20630-127	52U	1	Steel	Black Grey	RAL 7021	800mm
20630-128	52U	1	Steel	Black Grey	RAL 7021	800mm
20630-261	42U	1	Steel	Black Grey	RAL 7021	600mm
20630-262	47U	1	Steel	Black Grey	RAL 7021	600mm

Table 3/3	
Catalog Number	Depth
20630-065	600mm
20630-066	800mm
20630-067	900mm
20630-068	1000mm
20630-071	600mm

Catalog Number	Depth
20630-072	800mm
20630-073	900mm
20630-074	1000mm
20630-075	600mm
20630-076	800mm
20630-077	900mm
20630-078	1000mm
20630-079	600mm
20630-080	800mm
20630-081	900mm
20630-082	1000mm
20630-083	600mm
20630-084	800mm
20630-085	900mm
20630-086	1000mm
20630-087	600mm
20630-088	800mm
20630-089	900mm
20630-090	1000mm
20630-091	600mm
20630-092	800mm
20630-093	900mm
20630-094	1000mm
20630-095	600mm
20630-096	800mm
20630-097	900mm
20630-098	1000mm
20630-099	600mm
20630-100	800mm
20630-101	900mm
20630-102	1000mm
20630-103	1100mm
20630-104	1200mm
20630-105	600mm
20630-106	800mm

Catalog Number	Depth
20630-107	900mm
20630-108	1000mm
20630-109	1100mm
20630-110	1200mm
20630-111	600mm
20630-112	800mm
20630-113	900mm
20630-114	1000mm
20630-115	1100mm
20630-116	1200mm
20630-117	600mm
20630-118	800mm
20630-119	900mm
20630-120	1000mm
20630-121	1100mm
20630-122	1200mm
20630-123	1000mm
20630-124	1100mm
20630-125	1200mm
20630-126	1000mm
20630-127	1100mm
20630-128	1200mm
20630-261	300mm
20630-262	300mm

ADDITIONAL PRODUCT DETAILS

Castor can be added to the frame. If you will need a castor for your application, you can order a mobile frame which include castors.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER