



NVENT CADDY SPEED LINK SLS WITH WEDGE ANCHOR



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and wedge anchor from Powers Fasteners, Inc.

Quickly and easily attaches into cracked and non-cracked concrete

Installs in strut profiles without the need to insert fingers or tools into the strut

Finger tightening of nut secures the locking device into position without tools

No special tools required

ETA-13/0355 assessment available for wedge anchor from Powers Fasteners, Inc

SPECIFICATIONS

Wire Rope Diameter:	2 mm
Static Load Safety Factor:	5:1
Finish:	Electrogalvanized
Material:	Steel;Polypropylene;Zinc Alloy
Complies With:	SMACNA HVAC-DCS

Table 1/2

Catalog Number	Article Number	Wire Rope Length	Length (L)	Drill Bit Diameter	Drill Hole Depth	Embedment Depth
SLS2L3WA6	196759	3m	63.5 mm	6mm	60mm	55 mm Min
SLS2L5WA6	196760	5m	63.5 mm	6mm	60mm	55 mm Min

Table 2/2

Catalog Number	Article Number	Static Load (F)
SLS2L3WA6	196759	270N
SLS2L5WA6	196760	270N

Slot Size (SS): 8 x 6.5 mm - 8 x 10 mm

Hole Size (HS): 8 - 10 mm

Width (W): 16 mm

Height 2 (H2): 43.5mm

Height 1 (H1): 53mm

Thread Size (TS): M8


Thickness (T): 4 mm Max

ADDITIONAL PRODUCT DETAILS

The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

Total load per wire on a multi-tier trapeze must not exceed static load.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER