


19" FRONT PANEL, VENTED

Vented front panels allows heat dissipation through holes.



CERTIFICATIONS



FEATURES

Vented front panels (Aluminum) allows heat dissipation

SPECIFICATIONS

Accessory Type: Front panel

Table 1/3

Catalog Number	Type	Mounting	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30118-962	19" Front Panel	Screw-on Front	Painted	Painted		No
30702-044	19" Front Panel	Screw-on Front	Raw	Conductive		No
30702-047	19" Front Panel	Screw-on Front	Anodized	Anodized	Yes	No
30702-056	19" Front Panel	Screw-on Front	Painted	Painted		No
30118-963	19" Front Panel	Screw-on Front	Painted	Painted		No
30118-964	19" Front Panel	Screw-on Front	Painted	Painted		No
30702-045	19" Front Panel	Screw-on Front	Raw	Raw		No

Catalog Number	Type	Mounting	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30702-046	19" Front Panel	Screw-on Front	Raw	Raw		No
30702-048	19" Front Panel	Screw-on Front	Anodized	Anodized	Yes	No
30702-049	19" Front Panel	Screw-on Front	Anodized	Anodized	Yes	No
30702-057	19" Front Panel	Screw-on Front	Painted	Painted		No
30702-058	19" Front Panel	Screw-on Front	Painted	Painted		No

Table 2/3						
Catalog Number	Rack Width	Product Type	Height (H)	Works With	Rack Height	Package Quantity
30118-962	95HP	Front Panel	43.6mm	Cabinet, Wallmount Cases, 19" cases	1U	1
30702-044	95HP	Front Panel	43.6mm	Cabinet, Wallmount Cases, 19" cases	1U	1
30702-047	95HP	Front Panel	43.6mm	Cabinet, Wallmount Cases, 19" cases	1U	1
30702-056	95HP	Front Panel	43.6mm	Cabinet, Wallmount Cases, 19" cases	1U	1
30118-963	95HP	Front Panel	88.1mm	Cabinet, Wallmount Cases, 19" cases	2U	1
30118-964	95HP	Front Panel	132.5mm	Cabinet, Wallmount Cases, 19" cases	3U	1
30702-045	95HP	Front Panel	88.1mm	Cabinet, Wallmount Cases, 19" cases	2U	1
30702-046	95HP	Front Panel	132.5mm	Cabinet, Wallmount Cases, 19" cases	3U	1


Catalog Number	Rack Width	ProductType	Height (H)	Works With	Rack Height	Package Quantity
30702-048	95HP	Front Panel	88.1mm	Cabinet, Wallmount Cases, 19" cases	2U	1
30702-049	95HP	Front Panel	132.5mm	Cabinet, Wallmount Cases, 19" cases	3U	1
30702-057	95HP	Front Panel	88.1mm	Cabinet, Wallmount Cases, 19" cases	2U	1
30702-058	95HP	Front Panel	132.5mm	Cabinet, Wallmount Cases, 19" cases	3U	1

Table 3/3

Catalog Number	Finish	Material	Color	Color Code	Width (W)
30118-962	Powder Coated	Aluminum	Light Grey	RAL 7021	483mm
30702-044	Anodized	Aluminum			483mm
30702-047	Anodized	Aluminum			483mm
30702-056	Powder Coated	Aluminum	Black Grey	RAL 7035	483mm
30118-963	Anodized	Aluminum	Light Grey	RAL 7021	483mm
30118-964	Powder Coated	Aluminum	Light Grey	RAL 7021	483mm
30702-045	Anodized	Aluminum			483mm
30702-046	Anodized	Aluminum			483mm
30702-048	Anodized	Aluminum			483mm
30702-049	Anodized	Aluminum			483mm
30702-057	Powder Coated	Aluminum	Black Grey	RAL 7035	483mm
30702-058	Powder Coated	Aluminum	Black Grey	RAL 7035	483mm

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.



nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF

TRACER