

INTERNAL SIDE PANELS FOR POWER DISTRIBUTION, MSPS



The galvanised steel internal side panels, MSPS, segregate vertical sections and allow for mounting of busbar supports, MSHS, as well as other accessories. It is a flexible solution both for fix and plug in systems and allows for meeting form 4 segregation according to IEC 61439.

FEATURES

Description: Internal side panels to build up sections as from the enclosure frame. Frame hole pattern is needed in front, rear, top and bottom.

Material: 1.5 mm galvanized steel.

Delivery: 1 piece with mounting material.

The side panels segregate vertical sections, allowing customer's to mount main busbar supports (MSHS) and other accessories

A flexible solution for both fix and plug-in systems

The side panels allow customers to build up power distribution configurations to meet form 4 segregation according to IEC 61439

Hole patterns are required in the top, bottom, front and rear of the enclosure, in order to mount the internal side panels

SPECIFICATIONS

Thickness: 1.5mm
Finish: Galvanized
Material: Steel

Table 1/1

Catalog Number	Height	Width	Depth	Panel Size	Usage	Enclosure Material
MSPS1803	1800mm	88.5mm	300mm	1800 x 337mm	Cables Section	Mild Steel
MSPS1805	1800mm	88.5mm	500mm	1800 x 337mm	Cables Section	Mild Steel
MSPS1806	1800mm	26mm	600mm	1800 x 507mm	Compartments Section	Mild Steel
MSPS1806F	1800mm	26mm	600mm	1800 x 507mm	Compartments Section with Front Opening	Mild Steel
MSPS1808	1800mm	26mm	800mm	1800 x 507mm	Compartments Section	Mild Steel
MSPS1808F	1800mm	26mm	800mm	1800 x 507mm	Compartments Section with Front Opening	Mild Steel
MSPS2003	2000mm	88.5mm	300mm	2000 x 337mm	Cables Section	Mild Steel
MSPS2005	2000mm	88.5mm	500mm	2000 x 337mm	Cables Section	Mild Steel
MSPS2006	2000mm	26mm	600mm	2000 x 507mm	Compartments Section	Mild Steel
MSPS2006F	2000mm	26mm	600mm	2000 x 507mm	Compartments Section with Front Opening	Mild Steel
MSPS2008	2200mm	26mm	800mm	2200 x 507mm	Compartments Section	Mild Steel
MSPS2008F	2000mm	26mm	800mm	2000 x 507mm	Compartments Section with Front Opening	Mild Steel
MSPS2203	2200mm	88.5mm	300mm	2200 x 337mm	Cables Section	Mild Steel
MSPS2205	2200mm	88.5mm	500mm	2200 x 337mm	Cables Section	Mild Steel
MSPS2206	2200mm	26mm	600mm	2200 x 507mm	Compartments Section	Mild Steel
MSPS2206F	2200mm	26mm	600mm	2200 x 507mm	Compartments Section with Front Opening	Mild Steel
MSPS2208	2200mm	26mm	800mm	2200 x 507mm	Compartments Section	Mild Steel
MSPS2208F	2200mm	26mm	800mm	2200 x 507mm	Compartments Section with Front Opening	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER