



# NVENT CADDY PYRAMID UNIVERSAL SUPPORT



## FEATURES

- Captive stainless steel nuts allow for custom attachment methods to the support base including easy attachment of stainless steel strut, threaded rod or other project-specific hardware
- Foam bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Multiple sizes and load ratings offer the ability to tailor the solution to the application
- Includes square holes for creating an H-Frame with a 12" (305 mm) cross support (PBU16 only)
- Base is manufactured from UV-stabilized thermoplastic material

## SPECIFICATIONS

- Static Load Safety Factor:** 3:1
- Material:** Polyethylene;Polypropylene;Stainless Steel 18-8 (EN 1.4305)
- Temperature:** -45 to 65 °C


Table 1/2

Catalog Number	Article Number	Length 1 (L1)	Length 2 (L2)	Height (H)	Width (W)	Thread Size (TS)
PBU6M	360495	140 mm	196 mm	102 mm	150 mm	M10
PBU10M	360496	254 mm	318 mm	102 mm	201 mm	M10
PBU16M	360497	406 mm	480 mm	102 mm	201 mm	M10

Table 2/2

Catalog Number	Article Number	Hole Quantity	A	B	Surface Area	Static Load (F)
PBU6M	360495	3	114 mm	57 mm	26452mm <sup>2</sup>	1330N
PBU10M	360496	2	218 mm		59355mm <sup>2</sup>	4450N
PBU16M	360497	2	165 mm		91613mm <sup>2</sup>	6670N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**