


## HORIZONTAL RAIL INSULATION STRIP



Strip enables an insulated mounting of backplanes or metal plates as supports for connectors. Creates standardized mounting depth for plug-in units in the subrack in conjunction with L-ST and H-ST horizontal rails. Suitable for RatiopacPRO/-AIR, Propac Pro, CompacPRO and EuropacPRO/-Rugged.

### CERTIFICATIONS



### FEATURES

For insulated mounting of backplanes or metal plates as supports for connectors

Creates standardised mounting depth for plug-in units in the subrack in conjunction with L-ST and H-ST horizontal rails

### SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Width | Flammability Rating | Package Quantity | Product Type     | Product Family  | Works With      |
|----------------|------------|---------------------|------------------|------------------|---|-----------------|
| 24560-820      | 20 HP      | UL® 94V-0           | 10               | Insulation Strip | EuropacPRO,<br>RatiopacPRO,<br>RatiopacPRO<br>AIR,<br>CompacPRO,<br>PropacPRO,<br>Inpac | Subracks, Cases |

| Catalog Number | Rack Width | Flammability Rating | Package Quantity | ProductType      | Product Family  | Works With      |
|----------------|------------|---------------------|------------------|------------------|---|-----------------|
| 24560-884      | 84 HP      | UL® 94V-0           | 10               | Insulation Strip | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac | Subracks, Cases |
| 24560-828      | 28 HP      | UL® 94V-0           | 10               | Insulation Strip | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac | Subracks, Cases |
| 24560-840      | 40 HP      | UL® 94V-0           | 10               | Insulation Strip | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac | Subracks, Cases |
| 24560-842      | 42 HP      | UL® 94V-0           | 10               | Insulation Strip | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac | Subracks, Cases |
| 24560-863      | 63 HP      | UL® 94V-0           | 10               | Insulation Strip | EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Inpac | Subracks, Cases |

| Table 2/2      |               |           |
|----------------|---------------|-----------|
| Catalog Number | Material      | Length    |
| 24560-820      | Polycarbonate | 101.5 mm  |
| 24560-884      | Polycarbonate | 428.64 mm |
| 24560-828      | Polycarbonate | 144.2 mm  |
| 24560-840      | Polycarbonate | 205.12 mm |
| 24560-842      | Polycarbonate | 210.4 mm  |
| 24560-863      | Polycarbonate | 316.88 mm |

## ADDITIONAL PRODUCT DETAILS

---

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**