

SLOTTED FRONT PANELS FOR POWER DISTRIBUTION, MSMCP



This mild steel slotted front panel, MSMCP, is for the front frame of a fix system, or modular frames. No machining is required when it is used for mounting modular components.

FEATURES

Description: Slotted front panel for modular assemblies. Provided with one DIN rail per row for modular components. It has a top and bottom bending to provide extra rigidity.

Material: 1.25 mm steel.

Finish: RAL 7035 structured powder coating.

Delivery: 1 piece with mounting material.

Mounting requirements: To be assembled on the modular system frame.

The panels are to be mounted onto a fix system front frame (MSFCP) or onto modular system frames (MSMSF or MSMSM)

Slotted front panel for modular assemblies

Provided with one DIN rail per row for modular components

It has a top and bottom bending to provide extra rigidity

One piece with mounting material

To be assembled on the modular system frame

SPECIFICATIONS

| | |
|--------------------|---------------|
| Thickness: | 1.25mm |
| Color: | Light Gray |
| Material: | Mild Steel |
| Finish: | Powder Coated |
| Color Code: | RAL 7035 |

Table 1/1

| Catalog Number | Height | Width | Depth | Enclosure Material | Product Family | Panel Quantity |
|----------------|--------|-------|-------|--------------------|-----------------------------|----------------|
| MSMCP1506R5 | 150mm | 600mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 1 |
| MSMCP1508R5 | 150mm | 800mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 1 |
| MSMCP2006R5 | 200mm | 600mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 1 |
| MSMCP2008R5 | 200mm | 800mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 1 |
| MSMCP3006-1R5 | 300mm | 600mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 1 |
| MSMCP3006-2R5 | 300mm | 800mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 2 |
| MSMCP3008-1R5 | 300mm | 600mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 1 |
| MSMCP3008-2R5 | 300mm | 800mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 2 |
| MSMCP4506R5 | 450mm | 600mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 3 |
| MSMCP4508R5 | 450mm | 800mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 3 |
| MSMCP6006R5 | 600mm | 600mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 4 |
| MSMCP6008R5 | 600mm | 800mm | 13mm | Mild Steel | Free-Standing, Wall Mounted | 4 |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER