


## FRONT PANEL EMC TEXTILE SHIELDING KIT, -40 UP TO +85°C



The textile EMC gaskets are inserted into a slot on the right hand side of the U-shaped front panels. The gaskets are glued to the front panel. For an expanded temperature range up to +85°C.

### CERTIFICATIONS



### FEATURES

Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.

Profile seal is bonded onto the contact surface of the 19" bracket or of the rear angle and sets up the conductive connection to the U-shaped front panels

Temperature range -40 °C ... +85 °C

### SPECIFICATIONS

Table 1/1

Catalog Number	Package Quantity	Product Type	Product Family	Works With	Rack Height
21102-857	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	2 U

CatalogNumber	Package Quantity	Product Type	Product Family	Works With	Rack Height
21102-853	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	3 U
21102-854	100	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	3 U
21102-858	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	4 U
21102-978	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	5 U
21102-855	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	6 U
21102-856	100	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	6 U
21102-859	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	9 U

## ADDITIONAL PRODUCT DETAILS

EMC gaskets (textile) are required for shielding the front panels.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**