

VARISTAR COLOCATION CABINET, RAL 9003



Colocation cabinets with 2, 3 or 4 divider units in RAL 9003 to accommodate servers while separating access and cabling of the compartments.

CERTIFICATIONS



FEATURES

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 9003

SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Frame Color	Frame Material	Frame Color Code	Cladding Material	Cladding Color
12130-202	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-203	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-204	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-205	Rack	Signal White	Steel	RAL 7021	Steel	Signal White

Catalog Number	ProductType	Frame Color	Frame Material	Frame Color Code	Cladding Material	Cladding Color
12130-206	Rack	Black Grey	Steel	RAL 7021	Steel	Signal White
12130-207	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-208	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-209	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-210	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-211	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-212	Rack	Black Grey	Steel	RAL 7021	Steel	Signal White
12130-213	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-214	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-215	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-216	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-217	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-218	Rack	Black Grey	Steel	RAL 7021	Steel	Signal White
12130-219	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-220	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-221	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-222	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-223	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-224	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-225	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-257	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-258	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-259	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-260	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-261	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-262	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-269	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-270	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-271	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-272	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-273	Rack	Signal White	Steel	RAL 7021	Steel	Signal White
12130-274	Rack	Signal White	Steel	RAL 7021	Steel	Signal White

Table 2/3

Catalog Number	Cladding Color Code	Number of Compartments	Static Load	Height	Rack Height	Material
12130-202	RAL 9003	2	800kgf	2000mm	40U	Steel
12130-203	RAL 9003	3	800kgf	2000mm	39U	Steel
12130-204	RAL 9003	4	800kgf	2000mm	40U	Steel
12130-205	RAL 9003	2	800kgf	2000mm	40U	Steel
12130-206	RAL 9003	3	800kgf	2000mm	39U	Steel
12130-207	RAL 9003	4	800kgf	2000mm	40U	Steel
12130-208	RAL 9003	2	800kgf	2200mm	44U	Steel
12130-209	RAL 9003	3	800kgf	2200mm	45U	Steel
12130-210	RAL 9003	4	800kgf	2200mm	44U	Steel
12130-211	RAL 9003	2	800kgf	2200mm	44U	Steel
12130-212	RAL 9003	3	800kgf	2200mm	45U	Steel
12130-213	RAL 9003	4	800kgf	2200mm	44U	Steel
12130-214	RAL 9003	2	800kgf	2000mm	40U	Steel
12130-215	RAL 9003	3	800kgf	2000mm	39U	Steel
12130-216	RAL 9003	4	800kgf	2000mm	40U	Steel
12130-217	RAL 9003	2	800kgf	2000mm	40U	Steel
12130-218	RAL 9003	3	800kgf	2000mm	39U	Steel
12130-219	RAL 9003	4	800kgf	2000mm	40U	Steel
12130-220	RAL 9003	2	800kgf	2200mm	44U	Steel
12130-221	RAL 9003	3	800kgf	2200mm	45U	Steel
12130-222	RAL 9003	4	800kgf	2200mm	44U	Steel
12130-223	RAL 9003	2	800kgf	2200mm	44U	Steel
12130-224	RAL 9003	3	800kgf	2200mm	45U	Steel
12130-225	RAL 9003	4	800kgf	2200mm	44U	Steel
12130-257	RAL 9003	2	800kgf	2450mm	45U	Steel
12130-258	RAL 9003	3	800kgf	2450mm	48U	Steel
12130-259	RAL 9003	4	800kgf	2450mm	48U	Steel
12130-260	RAL 9003	2	800kgf	2450mm	45U	Steel
12130-261	RAL 9003	3	800kgf	2450mm	48U	Steel
12130-262	RAL 9003	4	800kgf	2450mm	48U	Steel
12130-269	RAL 9003	2	800kgf	2450mm	45U	Steel
12130-270	RAL 9003	3	800kgf	2450mm	48U	Steel
12130-271	RAL 9003	4	800kgf	2450mm	48U	Steel

Catalog Number	Cladding Color Code	Number of Compartments	Static Load	Height	Rack Height	Material
12130-272	RAL 9003	2	800kgf	2450mm	45U	Steel
12130-273	RAL 9003	3	800kgf	2450mm	48U	Steel
12130-274	RAL 9003	4	800kgf	2450mm	48U	Steel

Table 3/3				
Catalog Number	Package Quantity	Finish	Width	Depth
12130-202	1	Powder Coated	600mm	1000mm
12130-203	1	Powder Coated	600mm	1000mm
12130-204	1	Powder Coated	600mm	1000mm
12130-205	1	Powder Coated	800mm	1000mm
12130-206	1	Powder Coated	800mm	1000mm
12130-207	1	Powder Coated	800mm	1000mm
12130-208	1	Powder Coated	600mm	1000mm
12130-209	1	Powder Coated	600mm	1000mm
12130-210	1	Powder Coated	600mm	1000mm
12130-211	1	Powder Coated	800mm	1000mm
12130-212	1	Powder Coated	800mm	1000mm
12130-213	1	Powder Coated	800mm	1000mm
12130-214	1	Powder Coated	600mm	1200mm
12130-215	1	Powder Coated	600mm	1200mm
12130-216	1	Powder Coated	600mm	1200mm
12130-217	1	Powder Coated	800mm	1200mm
12130-218	1	Powder Coated	800mm	1200mm
12130-219	1	Powder Coated	800mm	1200mm
12130-220	1	Powder Coated	600mm	1200mm
12130-221	1	Powder Coated	600mm	1200mm
12130-222	1	Powder Coated	600mm	1200mm
12130-223	1	Powder Coated	800mm	1200mm
12130-224	1	Powder Coated	800mm	1200mm
12130-225	1	Powder Coated	800mm	1200mm
12130-257	1	Powder Coated	600mm	1000mm
12130-258	1	Powder Coated	600mm	1000mm
12130-259	1	Powder Coated	600mm	1000mm
12130-260	1	Powder Coated	800mm	1000mm

Catalog Number	Package Quantity	Finish	Width	Depth
12130-261	1	Powder Coated	800mm	1000mm
12130-262	1	Powder Coated	800mm	1000mm
12130-269	1	Powder Coated	600mm	1200mm
12130-270	1	Powder Coated	600mm	1200mm
12130-271	1	Powder Coated	600mm	1200mm
12130-272	1	Powder Coated	800mm	1200mm
12130-273	1	Powder Coated	800mm	1200mm
12130-274	1	Powder Coated	800mm	1200mm

ADDITIONAL PRODUCT DETAILS

Side panel must be ordered separately. For suitable cable panel see Accessories.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER