

LOCKING SYSTEM FOR LIFT HANDLES, LHC



The locking inserts and cylinders can be mounted independently in the lift handle, which means many combinations can be created. This reduces the number of handles to be stocked.

FEATURES

Description: Profile half cylinder locks. To be used in the lift handles LHC.

Pack quantity: 1 piece.

SPECIFICATIONS

Color: Black Gray
Finish: Smooth Matte

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Key Type	Key Code
LHC526	LHC526	37mm	23mm	41mm	Triangle 7 mm	
LHC533	LHC533	37mm	23mm	41mm	Cylinder N°E1 (VW), key excluded	
LHC521	LHC521	37mm	23mm	41mm	Ronis	C21323
LHC522	LHC522	37mm	23mm	41mm	Ronis	C21323
LHC523	LHC523	37mm	23mm	41mm	Square 7 mm	
LHC524	LHC524	37mm	23mm	41mm	Square 8 mm	
LHC527	LHC527	37mm	23mm	41mm	Triangle 8 mm	
LHC528	LHC528	37mm	23mm	41mm	Double-bit 3 mm	
LHC529	LHC529	37mm	23mm	41mm	Double-bit 5 mm	
LHC530	LHC530	37mm	23mm	41mm	Daimler Benz	
LHC534	LHC534	37mm	23mm	41mm	Adapter for other profile half cylinders (DIN18252)	
LHC535	LHC535	37mm	23mm	41mm	Adapter for ASSA ABLOY and Trioving cylinders	
LHC536	LHC536	37mm	23mm	41mm	Push button only	
LHC5212132E	LHC5212132E	37mm	23mm	41mm	Ronis	2132E
LHC5213121E	LHC5213121E	37mm	23mm	41mm	Ronis	3121E
LHC531	LHC531	37mm	23mm	41mm	Lock insert slotted 2x4 mm	

ADDITIONAL PRODUCT DETAILS

* Other key numbers available on request. ** Key numbers 333, 1333, EK333 and GX130 are equal. *** Order separate key LSMK for Square 8 mm and Triangle 8 mm.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER