


## CPCI SYSTEM WITH ATX PSU, 3 U, 8 SLOT

### CATALOG NUMBER

**24579-031**



Fanless 3U CompactPCI System with vertical Card Cage for eight 3U Boards and eight RTM Boards. With built in ATX Power Supply.

### CERTIFICATIONS



### FEATURES

In accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG 2.0 rev. 3.0

System with vertical card cage. Board format Front: 3 U, 160 mm deep; Rear I/O: 3 U, 80 mm deep

Backplane 8 slot, 3 U, 32 bit; system slot right; 8 HP wide CPU can be used

Heat dissipation by convection, airflow bottom to top

ATX PSU, 300 W

### PRODUCT ATTRIBUTES

Product Type: System

Number of Slots: 8

Type: 19" Rack Mount

Backplane Type: 3 U CompactPCI

Data Transfer: 32-bit PCI Bus

Power per Slot: 10W
Input Voltage AC: 100 – 240V
Rack Height: 3U
Power Supply Type: (1) ATX PSU
Power Supply Included: Yes
Rear I/O: Yes
Complies With: PICMG 2.0 R3.0
Depth: 275mm
Height: 132.55mm
Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Modified systems available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

<b>North America</b> All locations +1.763.422.2661 Chat with us: <a href="http://schroff.nvent.com">schroff.nvent.com</a>	<b>Europe</b> Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: <a href="http://schroff.nvent.com">schroff.nvent.com</a>	<b>Asia</b> Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: <a href="http://schroff.nvent.com">schroff.nvent.com</a>	<b>Middle East &amp; India</b> Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: <a href="http://schroff.nvent.com">schroff.nvent.com</a>
---	---	---	---