


## AMC FRONT PANEL WITH PULL HANDLE



AdvancedMC Front Panel including EMC gasket for AMC.0 Rev. 2.0 Modules.

### CERTIFICATIONS



### FEATURES

In accordance with AMC.0 R2.0 specification

Front panel for pull-handle mechanism (with cut-outs for light pipe)

For the use together with the AMC Pull-handle mechanism, AMC.0 R2.0

### SPECIFICATIONS

**Accessory Type:** Front panel

Table 1/2


Catalog Number	Front Finish	Rear Finish	Material	Rack Width	Width (W)	Depth (D)
30849-402	Raw	Raw	Stainless Steel	3HP	13.9mm	1mm
30849-403	Raw	Raw	Stainless Steel	4HP	19mm	1mm
30849-404	Raw	Raw	Stainless Steel	6HP	29mm	1mm
30849-406	Raw	Raw	Stainless Steel	4HP	19mm	1mm
30849-407	Raw	Raw	Stainless Steel	6HP	29mm	1mm
30849-658	Raw	Raw	Aluminum	4HP	19mm	2.5mm

Catalog Number	Front Finish	Rear Finish	Material	Rack Width	Width (W)	Depth (D)
30849-670	Raw	Raw	Aluminum	4HP	19mm	2.5mm
30849-682	Raw	Raw	Aluminum	6HP	29mm	2.5mm
30849-694	Raw	Raw	Aluminum	6HP	29mm	2.5mm

Table 2/2

Catalog Number	Height (H)	Package Quantity	Finish
30849-402	73.8mm	1	
30849-403	73.8mm	1	
30849-404	73.8mm	1	
30849-406	148.8mm	1	
30849-407	148.8mm	1	
30849-658	73.8mm	1	Passivated
30849-670	148.8mm	1	Passivated
30849-682	73.8mm	1	Passivated
30849-694	148.8mm	1	Passivated

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**