


# PLUG-IN UNIT KIT FOR FMC, CHROMATED, SHIELDED (TEXTILE) WITH HANDLE



The FMC bezel are in accordance with Vita 57.1 specification.  
Covers the cut out in the overall front panel.

## CERTIFICATIONS



## FEATURES

In accordance with Vita 57.1 specification

For single 69.0 x 76.5 mm or double 139.0 x 76.5 mm modules

Al-Profile plug-in unit with IEL handle

## SPECIFICATIONS

Table 1/3

Catalog Number	Type	Handle Type	Mounting	EMC Shielding	EMC Gasket Type	Material
----------------	------	-------------	----------	---------------	-----------------	----------

20836-253	Front Panel with Handle (PIU)	IEL	Screw-on Front	Yes	Textile	Aluminum
20836-254	Front Panel with Handle (PIU)	IEL	Screw-on Front	Yes	Textile	Aluminum

Table 2/3						
Catalog Number	Front Finish	Rear Finish	Treated Edges	Rack Height	Height	Rack Width
20836-253	Anodized	Conductive	No	3U	128.4mm	4HP
20836-254	Anodized	Conductive	No	6U	261.8mm	4HP

Table 3/3				
Catalog Number	Width	Complies With	Package Quantity	Finish
20836-253	20mm	FMC Mezzanine, Vita 57.1	1	Anodized, Passivated
20836-254	20mm	FMC Mezzanine, Vita 57.1	1	Anodized, Passivated

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**