

SOCKET STRIP, SCHUKO, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



FEATURES

Installation height 1 U

Output via SCHUKO sockets

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

Horizontal or vertical mounting

In accordance with DIN 57620

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-343	Socket Strip	SCHUKO	8	No	Grey	230V
60110-344	Socket Strip	SCHUKO	8	No	Black	230V
60110-345	Socket Strip	SCHUKO	8	No	Red	230V
60110-352	Socket Strip	SCHUKO	6	No	Grey	230V

Catalog Number	ProductType	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-353	Socket Strip	SCHUKO	6	No	Black	230V
60110-354	Socket Strip	SCHUKO	6	No	Red	230V

Table 2/2						
Catalog Number	Function	Length	Depth	Material	Finish	Package Quantity
60110-343		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-344		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-345		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-352	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-353	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-354	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER