


VARISTAR DECO FRAME ADAPTER BRACKET



Adapter Brackets are helpful in assembling slide rails and shelves for a nopen frame Varistar cabinet with deco frame.

CERTIFICATIONS



FEATURES

For assembling slide rails and shelves in Varistar Deco

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Works With	Color	Color Code	Rack Height	Height
23130-220	Bracket	Varistar, Varistar CP	Black Grey	RAL 7021	24U	1200mm
23130-221	Deco Frame Bracket	Cabinet, Varistar CP	Black Grey	RAL 7021	29U	1400mm
23130-222	Deco Frame Bracket	Cabinet, Varistar CP	Black Grey	RAL 7021	33U	1600mm
23130-223	Deco Frame Bracket	Cabinet, Varistar CP	Black Grey	RAL 7021	38U	1800mm
23130-224	Deco Frame Bracket	Cabinet, Varistar CP	Black Grey	RAL 7021	42U	2000mm
23130-225	Deco Frame Bracket	Cabinet, Varistar CP	Black Grey	RAL 7021	47U	2200mm
23130-230	Deco Frame Bracket	Cabinet	Light Grey	RAL 7035	24U	1200mm
23130-231	Deco Frame Bracket	Cabinet	Light Grey	RAL 7035	29U	1400mm
23130-232	Deco Frame Bracket	Cabinet	Light Grey	RAL 7035	33U	1600mm
23130-233	Deco Frame Bracket	Cabinet	Light Grey	RAL 7035	38U	1800mm
23130-234	Deco Frame Bracket	Cabinet	Light Grey	RAL 7035	42U	2000mm
23130-235	Deco Frame Bracket	Cabinet	Light Grey	RAL 7035	47U	2200mm

Table 2/2

Catalog Number	Width	Material	Finish	Package Quantity
23130-220	600mm	Steel	Powder Coated	2
23130-221	600mm	Steel	Powder Coated	2
23130-222	600mm	Steel	Powder Coated	2
23130-223	600mm	Steel	Powder Coated	2
23130-224	600mm	Steel	Powder Coated	2
23130-225	600mm	Steel	Powder Coated	2
23130-230	600mm	Steel	Powder Coated	2
23130-231	600mm	Steel	Powder Coated	2
23130-232	600mm	Steel	Powder Coated	2
23130-233	600mm	Steel	Powder Coated	2
23130-234	600mm	Steel	Powder Coated	2

Catalog Number	Width	Material	Finish	Package Quantity
23130-235	600mm	Steel	Powder Coated	2

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER