



## SOSR STAND OFF TWO HOLE STRAP FOR CPVC PIPE



### CERTIFICATIONS



### FEATURES

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Positions pipe 1-1/2" (38 mm) off the mounting surface eliminating the need for wooden spacer blocks

Can be mounted in both vertical and horizontal positions on concrete, steel and wood

Meets the UL® 203 stringent upward thrust requirement

UL® Listed as both a hanger and pipe restraint

Complies with static load requirements of NFPA® 13

Includes mounting screws

Can be used with 3TW backing nut on composite wood joist installations

### SPECIFICATIONS

**Finish:** Pregalvanized

**Material:** Steel


Table 1/2

Catalog Number	Article Number	Pipe Size	NB/DN	Hole Size (HS)	A	B
SOSR075	597805	3/4"	20	5.1 mm	68 mm	92 mm
SOSR100	597806	1"	25	5.1 mm	75 mm	94 mm
SOSR125	597807	1 1/4"	32	5.1 mm	84 mm	92 mm
SOSR150	597808	1 1/2"	40	5.1 mm	98 mm	114 mm
SOSR200	597809	2"	50	5.1 mm	102 mm	133 mm

Table 2/2

Catalog Number	Article Number	C	Thickness (T)	Hanger Spacing	Packing Quantity
SOSR075	597805	25.4 mm	1.3 mm	1.65 m Max	1.0000
SOSR100	597806	25.4 mm	1.3 mm	1.8 m Max	1.0000
SOSR125	597807	25.4 mm	1.61 mm	1.95 m Max	1.0000
SOSR150	597808	25.4 mm	1.61 mm	2.1 m Max	1.0000
SOSR200	597809	25.4 mm	1.61 mm	2.4 m Max	1.0000

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**