

PLUG-IN UNIT KIT WITH XL HANDLE, SHIELDED, BLACK, 6 U



The XL handle is used for applications which requires high insertion / extraction forces such as VPX or VXS standards. Suitable for insertion and extractions forces up to 1500N (per pair).

CERTIFICATIONS



FEATURES

For applications which requires high insertion / extraction forces such as VPX or VXS standards

Additional board fixing options available

Handle requires additional die cast fixing block (combination with horizontal rail short / long lip)

U-shaped front panel for textile gasket

Suitable for insertion/extraction forces up to 1500 N (per pair)

IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Handle Type	Mounting	EMC Shielding	EMC Gasket Type	Material
20848-769	Front Panel with Handle (PIU)	XL	Screw-on Front	Yes	Textile	Aluminum
20848-770	Front Panel with Handle (PIU)	XL	Screw-on Front	Yes	Textile	Aluminum

Catalog Number	Type	Handle Type	Mounting	EMC Shielding	EMC Gasket Type	Material
20848-771	Front Panel with Handle (PIU)	XL	Screw-on Front	Yes	Textile	Aluminum

Table 2/3

Catalog Number	Front Finish	Rear Finish	Treated Edges	Rack Height	Height (H)	Rack Width
20848-769	Anodized	Etched	No	6U	261.8mm	4HP
20848-770	Anodized	Etched	No	6U	261.8mm	8HP
20848-771	Anodized	Etched	No	6U	261.8mm	12HP


Table 3/3

Catalog Number	Width (W)	Complies With	Package Quantity	Finish
20848-769	20mm	IEC 60297-3-102, IEEE 1101.10, IEEE 1101.1	1	Anodized, Passivated
20848-770	40.3mm	IEC 60297-3-102, IEEE 1101.10, IEEE 1101.1	1	Anodized, Passivated
20848-771	60.6mm	IEC 60297-3-102, IEEE 1101.10, IEEE 1101.1	1	Anodized, Passivated

ADDITIONAL PRODUCT DETAILS

Kit with front panel for micro switch on request.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation,

misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER