

## EUROPACPRO 19" SUBRACK KIT FOR BACKPLANE, LIGHT, UNSHIELDED

Non-EMC shielded subrack for backplane mounting, light version.



### CERTIFICATIONS



### FEATURES

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

### SPECIFICATIONS

Table 1/2

Catalog Number	For Mounting	Board Depth	EMC Shielding	Rack Width	Handle Included	Package Quantity
24564-131	Backplane	160 mm	No	84 HP	No	1
24564-132	Backplane	160 mm, 220 mm	No	84 HP	No	1

Catalog Number	ForMounting	Board Depth	EMC Shielding	Rack Width	Handle Included	Package Quantity
24564-133	Backplane	160 mm, 220 mm, 280 mm	No	84 HP	No	1
24564-431	Backplane	160 mm	No	84 HP	No	1
24564-432	Backplane	160 mm, 220 mm	No	84 HP	No	1
24564-433	Backplane	160 mm, 220 mm, 280 mm	No	84 HP	No	1

Table 2/2						
Catalog Number	Product Type	Rack Height	Complies With	Mounting	Depth	Static Load
24564-131	Subrack/Chassis	3 U	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Rack	175 mm	7.5 kgf
24564-132	Subrack/Chassis	3 U	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Rack	235 mm	7.5 kgf
24564-133	Subrack/Chassis	3 U	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Rack	295 mm	7.5 kgf
24564-431	Subrack/Chassis	6 U	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Rack	175 mm	7.5 kgf
24564-432	Subrack/Chassis	6 U	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Rack	235 mm	7.5 kgf
24564-433	Subrack/Chassis	6 U	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	Rack	295 mm	7.5 kgf

## ADDITIONAL PRODUCT DETAILS

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**