


## FRONT HANDLE ONE-PIECE, WIDTH 12.2 MM



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

### CERTIFICATIONS



### FEATURES

Static load-carrying capacity 30 kg/pair

Bolted from rear

### SPECIFICATIONS

Table 1/2

Catalog Number	Handle Type	Package Quantity	Type	Product Type	Product Family	Works With
10501-116	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-004	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-020	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-026	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-005	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-006	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-007	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-022	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks

Catalog Number	Handle Type	Package Quantity	Type	ProductType	Product Family	Works With
10501-029	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-008	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-016	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-021	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-018	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-025	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-027	Straight	1	Straight version	Handle	EuropacPRO	Subracks
10501-028	Straight	1	Straight version	Handle	EuropacPRO	Subracks

Table 2/2					
Catalog Number	Rack Height	Color	Material	Accessory Type	Torque
10501-116	1 U	Silver	Aluminum	Front panel	
10501-004	2 U	Silver	Aluminum	Front panel	
10501-020	3 U	Silver	Aluminum		2.4 N·m
10501-026	3 U	Black	Aluminum	Front panel	2.4 N·m
10501-005	3 U	Silver	Aluminum		2.4 N·m
10501-006	4 U	Silver	Aluminum	Front panel	
10501-007	5 U	Silver	Aluminum	Front panel	
10501-022	6 U	Silver	Aluminum		2.4 N·m
10501-029	6 U	Black	Aluminum	Front panel	2.4 N·m
10501-008	6 U	Silver	Aluminum		2.4 N·m
10501-016	2 U	Silver	Aluminum	Front panel	
10501-021	4 U	Silver	Aluminum		2.4 N·m
10501-018	4 U	Silver	Aluminum	Front panel	2.4 N·m
10501-025	2 U	Black	Aluminum	Front panel	
10501-027	4 U	Black	Aluminum	Front panel	
10501-028	5 U	Black	Aluminum	Front panel	

## ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**