


## U-PROFILE FRONT PANEL, SHIELDABLE, D-SUB CUTOUTS



U-profile front panel with cutout for D-Sub connectors.  
Shieldable for textile EMC gasket.

## CERTIFICATIONS



## FEATURES

U-profile, front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

## SPECIFICATIONS

Table 1/3						
Catalog Number	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30849-749	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-750	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP

Catalog Number	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30849-751	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-752	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-753	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-754	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-755	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP

Table 2/3						
Catalog Number	Package Quantity	Height	Product Type	Type	Rack Height	Width
30849-749	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-750	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-751	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-752	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-753	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-754	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-755	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm

Table 3/3			
Catalog Number	Complies With	Mounting	Material
30849-749	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30849-750	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30849-751	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30849-752	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30849-753	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum

Catalog Number	Complies With	Mounting	Material
30849-754	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum
30849-755	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminum

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order textile EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**