

TELECOM MAIN GROUNDING BUSBAR



CERTIFICATIONS



FEATURES

- Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations
- Complies with NEMA® standards
- Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)
- Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICATIONS


- Thickness (T):** 0.25in
- Width (W):** 4in
- Material:** Copper

Table 1/2						
Catalog Number	Length 1 (L1)	Length 2 (L2)	Tin Plating	Hole Size 1 Number of Pairs	Hole Size 2 Number of Pairs	A
TMGBA12L15P	12in	9in	No	15	3	1in
TMGBA12L15PT	12in	9in	Yes	15	3	1in

Catalog Number	Length 1(L1)	Length 2(L2)	Tin Plating	Hole Size 1 Number of Pairs	Hole Size 2 Number of Pairs	A
TMGBA16L19P	15.5in	9in	No	19	3	1in
TMGBA16L19PT	15.5in	9in	Yes	19	3	1in
TMGBA18L23P	17.75in	9in	No	23	3	1in
TMGBA18L23PT	17.75in	9in	Yes	23	3	1in
TMGBA20L27P	20in	9in	No	27	3	1in
TMGBA20L27PT	20in	9in	Yes	27	3	1in
TMGBA24L33P	24in	18in	No	33	5	1in
TMGBA24L33PT	24in	18in	Yes	33	5	1in
TMGBA29L41P	29in	18in	No	41	5	1in
TMGBA29L41PT	29in	18in	Yes	41	5	1in

Table 2/2					
Catalog Number	C	B	D	Hole Size 1 (HS1)	Hole Size 2 (HS2)
TMGBA12L15P	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA12L15PT	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA16L19P	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA16L19PT	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA18L23P	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA18L23PT	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA20L27P	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA20L27PT	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA24L33P	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA24L33PT	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA29L41P	0.625in	1.125in	0.625in	0.3125in	0.4375in
TMGBA29L41PT	0.625in	1.125in	0.625in	0.3125in	0.4375in

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER