

VARISTAR CP MOBILE FRAME



Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration. For mobile applications.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Frame Material	Static Load	Complies With	Product Type	Works With
20630-193	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-194	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-195	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-196	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-199	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-200	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-201	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-202	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-203	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Works With
20630-204	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-205	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-206	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-207	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-208	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-209	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-210	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-211	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-212	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-213	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-214	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-215	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-216	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-217	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-218	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-219	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-220	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-221	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-222	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-223	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Works With
20630-224	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-225	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-226	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-227	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-228	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-229	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-230	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-231	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-232	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-233	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-234	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-235	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-236	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-237	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-238	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-239	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-240	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-241	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-242	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-243	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP

Catalog Number	Type	Frame Material	Static Load	Complies With	ProductType	Works With
20630-244	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-245	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-246	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-247	Mobile	Steel		IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-248	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-249	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-250	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-251	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-252	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-253	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-254	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-255	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP
20630-256	Mobile	Steel	1600kgf	IEC 61587-1, IEC 61587-3	Cabinet/Rack Frame	Varistar CP

Table 2/2

Catalog Number	Rack Height	Package Quantity	Material	Color	Color Code
20630-193	24U	1	Steel	Black Grey	RAL 7021
20630-194	24U	1	Steel	Black Grey	RAL 7021
20630-195	24U	1	Steel	Black Grey	RAL 7021
20630-196	24U	1	Steel	Black Grey	RAL 7021
20630-199	24U	1	Steel	Black Grey	RAL 7021
20630-200	24U	1	Steel	Black Grey	RAL 7021
20630-201	24U	1	Steel	Black Grey	RAL 7021
20630-202	24U	1	Steel	Black Grey	RAL 7021
20630-203	29U	1	Steel	Black Grey	RAL 7021

CatalogNumber	Rack Height	Package Quantity	Material	Color	Color Code
20630-204	29U	1	Steel	Black Grey	RAL 7021
20630-205	29U	1	Steel	Black Grey	RAL 7021
20630-206	29U	1	Steel	Black Grey	RAL 7021
20630-207	29U	1	Steel	Black Grey	RAL 7021
20630-208	29U	1	Steel	Black Grey	RAL 7021
20630-209	29U	1	Steel	Black Grey	RAL 7021
20630-210	29U	1	Steel	Black Grey	RAL 7021
20630-211	33U	1	Steel	Black Grey	RAL 7021
20630-212	33U	1	Steel	Black Grey	RAL 7021
20630-213	33U	1	Steel	Black Grey	RAL 7021
20630-214	33U	1	Steel	Black Grey	RAL 7021
20630-215	33U	1	Steel	Black Grey	RAL 7021
20630-216	33U	1	Steel	Black Grey	RAL 7021
20630-217	33U	1	Steel	Black Grey	RAL 7021
20630-218	33U	1	Steel	Black Grey	RAL 7021
20630-219	38U	1	Steel	Black Grey	RAL 7021
20630-220	38U	1	Steel	Black Grey	RAL 7021
20630-221	38U	1	Steel	Black Grey	RAL 7021
20630-222	38U	1	Steel	Black Grey	RAL 7021
20630-223	38U	1	Steel	Black Grey	RAL 7021
20630-224	38U	1	Steel	Black Grey	RAL 7021
20630-225	38U	1	Steel	Black Grey	RAL 7021
20630-226	38U	1	Steel	Black Grey	RAL 7021
20630-227	42U	1	Steel	Black Grey	RAL 7021
20630-228	42U	1	Steel	Black Grey	RAL 7021
20630-229	42U	1	Steel	Black Grey	RAL 7021
20630-230	42U	1	Steel	Black Grey	RAL 7021
20630-231	42U	1	Steel	Black Grey	RAL 7021
20630-232	42U	1	Steel	Black Grey	RAL 7021
20630-233	42U	1	Steel	Black Grey	RAL 7021
20630-234	42U	1	Steel	Black Grey	RAL 7021
20630-235	42U	1	Steel	Black Grey	RAL 7021
20630-236	42U	1	Steel	Black Grey	RAL 7021
20630-237	42U	1	Steel	Black Grey	RAL 7021

CatalogNumber	Rack Height	Package Quantity	Material	Color	Color Code
20630-238	42U	1	Steel	Black Grey	RAL 7021
20630-239	47U	1	Steel	Black Grey	RAL 7021
20630-240	47U	1	Steel	Black Grey	RAL 7021
20630-241	47U	1	Steel	Black Grey	RAL 7021
20630-242	47U	1	Steel	Black Grey	RAL 7021
20630-243	47U	1	Steel	Black Grey	RAL 7021
20630-244	47U	1	Steel	Black Grey	RAL 7021
20630-245	47U	1	Steel	Black Grey	RAL 7021
20630-246	47U	1	Steel	Black Grey	RAL 7021
20630-247	47U	1	Steel	Black Grey	RAL 7021
20630-248	47U	1	Steel	Black Grey	RAL 7021
20630-249	47U	1	Steel	Black Grey	RAL 7021
20630-250	47U	1	Steel	Black Grey	RAL 7021
20630-251	52U	1	Steel	Black Grey	RAL 7021
20630-252	52U	1	Steel	Black Grey	RAL 7021
20630-253	52U	1	Steel	Black Grey	RAL 7021
20630-254	52U	1	Steel	Black Grey	RAL 7021
20630-255	52U	1	Steel	Black Grey	RAL 7021
20630-256	52U	1	Steel	Black Grey	RAL 7021

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER