

VARISTAR CP SWING FRAME FOR 800 MM WIDTH

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° / 160° movement and flexible pivot point.

CARACTERÍSTICAS

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks

120° / 160° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

ESPECIFICACIONES

Table 1/2

Número de catálogo	Altura	Product Type	Product Family	Rack Height	Ancho	Color
21630-669	1200 mm	Cabinet/Rack Frame	Varistar CP	24 U	800 mm	Black Grey
21630-680	1200 mm	Cabinet/Rack Frame	Varistar CP	24 U	800 mm	Black Grey
21630-671	1400 mm	Cabinet/Rack Frame	Varistar CP	29 U	800 mm	Black Grey
21630-681	1400 mm	Cabinet/Rack Frame	Varistar CP	29 U	800 mm	Black Grey
21630-673	1600 mm	Cabinet/Rack Frame	Varistar CP	33 U	800 mm	Black Grey
21630-682	1600 mm	Cabinet/Rack Frame	Varistar CP	33 U	800 mm	Black Grey
21630-675	1800 mm	Cabinet/Rack Frame	Varistar CP	38 U	800 mm	Black Grey
21630-683	1800 mm	Cabinet/Rack Frame	Varistar CP	38 U	800 mm	Black Grey
21630-677	2000 mm	Cabinet/Rack Frame	Varistar CP	42 U	800 mm	Black Grey

Número de catálogo	Altura	ProductType	Product Family	Rack Height	Ancho	Color
21630-684	2000 mm	Cabinet/Rack Frame	Varistar CP	42 U	800 mm	Black Grey
21630-679	2200 mm	Cabinet/Rack Frame	Varistar CP	47 U	800 mm	Black Grey
21630-685	2200 mm	Cabinet/Rack Frame	Varistar CP	47 U	800 mm	Black Grey

Table 2/2			
Número de catálogo	Material	Color Code	Protection Rating
21630-669	Acero	RAL 7021	IP20
21630-680	Acero	RAL 7021	IP20
21630-671	Acero	RAL 7021	IP20
21630-681	Acero	RAL 7021	IP20
21630-673	Acero	RAL 7021	IP20
21630-682	Acero	RAL 7021	IP20
21630-675	Acero	RAL 7021	IP20
21630-683	Acero	RAL 7021	IP20
21630-677	Acero	RAL 7021	IP20
21630-684	Acero	RAL 7021	IP20
21630-679	Acero	RAL 7021	IP20
21630-685	Acero	RAL 7021	IP20

ADDITIONAL PRODUCT DETAILS

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER