


FRONT PANEL, FLAT, UNSHIELDED, D-SUB CUTOUTS



Flat front panel with cutout for D-Sub connectors. Unshielded version.

CERTIFICATIONS



CARACTERÍSTICAS

Non-shielded version

Aluminum, 2.5 mm, front anodized, rear conductive

ESPECIFICACIONES

Table 1/3

Table 1/3						
Número de catálogo	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
30118-341	No	Anodizado	Conductive	No	4 HP	5
30118-342	No	Anodizado	Conductive	No	4 HP	5
30118-343	No	Anodizado	Conductive	No	4 HP	5
30118-344	No	Anodizado	Conductive	No	4 HP	5

Número de catálogo	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
30118-345	No	Anodizado	Conductive	No	4 HP	5
30118-346	No	Anodizado	Conductive	No	4 HP	5
30118-347	No	Anodizado	Conductive	No	4 HP	5

Table 2/3						
Número de catálogo	Altura	Product Type	Tipo	Rack Height	Ancho	Cumple con
30118-341	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-342	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-343	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-344	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-345	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-346	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30118-347	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10

Table 3/3		
Número de catálogo	Montaje	Material
30118-341	Screw-on Front	Aluminio
30118-342	Screw-on Front	Aluminio
30118-343	Screw-on Front	Aluminio
30118-344	Screw-on Front	Aluminio
30118-345	Screw-on Front	Aluminio
30118-346	Screw-on Front	Aluminio
30118-347	Screw-on Front	Aluminio

ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please order fixing material (sleeves, collar screws) separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER