

FRONT PANEL, FRONT ANODIZED, REAR CONDUCTIVE, UNSHIELDED

Front panel, unshielded, front anodized and rear conductive.



CERTIFICATIONS



CARACTERÍSTICAS

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

ESPECIFICACIONES

Table 1/3

Número de catálogo	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30847-469	Ninguno	No	Anodizado	Conductive	No	84 HP
30847-459	Ninguno	No	Anodizado	Conductive	No	42 HP
30847-460	Ninguno	No	Anodizado	Conductive	No	63 HP
30847-467	Ninguno	No	Anodizado	Conductive	No	42 HP
30847-468	Ninguno	No	Anodizado	Conductive	No	63 HP
30847-458	Ninguno	No	Anodizado	Conductive	No	28 HP
30838-043	Ninguno	No	Anodizado	Conductive	No	4 HP
30847-462	Ninguno	No	Anodizado	Conductive	No	28 HP

Número de catálogo	Handle Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30847-466	Ninguno	No	Anodizado	Conductive	No	28 HP

Table 2/3						
Número de catálogo	Package Quantity	Altura	Product Type	Tipo	Rack Height	Ancho
30847-469	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	426.4 mm
30847-459	1	84 mm	Front Panel	Front Panel without Handle	2 U	213 mm
30847-460	1	84 mm	Front Panel	Front Panel without Handle	2 U	319.7 mm
30847-467	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	213 mm
30847-468	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	319.7 mm
30847-458	5	84 mm	Front Panel	Front Panel without Handle	2 U	141.9 mm
30838-043	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30847-462	5	172.9 mm	Front Panel	Front Panel without Handle	4 U	141.9 mm
30847-466	5	217.4 mm	Front Panel	Front Panel without Handle	5 U	141.9 mm

Table 3/3				
Número de catálogo	Cumple con	Montaje	Material	Certificaciones
30847-469	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
30847-459	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
30847-460	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
30847-467	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
30847-468	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
30847-458	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
30838-043	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS

Número de catálogo	Cumple con	Montaje	Material	Certificaciones
30847-462	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
30847-466	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.