

VARISTAR CP PERFORATED DOOR, SEISMIC IP20, MULTI-POINT LOCKING

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

CARACTERÍSTICAS

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

ESPECIFICACIONES

Table 1/3

Número de catálogo	Locking Type	Altura	Product Type	Product Family	Works With	Tipo
21630-876	4-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-877	4-Point Locking	1600 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-878	4-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-879	4-Point Locking	1800 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-880	4-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-881	4-Point Locking	2000 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-882	5-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated
21630-883	5-Point Locking	2200 mm	Cabinet Door	Varistar CP	Varistar CP	Steel Door, Perforated

Table 2/3

Número de catálogo	Rack Height	Ancho	Cumple con	Color	Material	Color Code
21630-876	33 U	600 mm	IEC 61587-1, IEC 61587-2	Black Grey	Acero	RAL 7021

Número de catálogo	Rack Height	Ancho	Cumple con	Color	Material	Color Code
21630-877	33 U	800 mm	IEC 61587-1, IEC 61587-2	Black Grey	Acero	RAL 7021
21630-878	38 U	600 mm	IEC 61587-1, IEC 61587-2	Black Grey	Acero	RAL 7021
21630-879	38 U	800 mm	IEC 61587-1, IEC 61587-2	Black Grey	Acero	RAL 7021
21630-880	42 U	600 mm	IEC 61587-1, IEC 61587-2	Black Grey	Acero	RAL 7021
21630-881	42 U	800 mm	IEC 61587-1, IEC 61587-2	Black Grey	Acero	RAL 7021
21630-882	47 U	600 mm	IEC 61587-1, IEC 61587-2	Black Grey	Acero	RAL 7021
21630-883	47 U	800 mm	IEC 61587-1, IEC 61587-2	Black Grey	Acero	RAL 7021

Table 3/3

Número de catálogo	Protection Rating
21630-876	IP20
21630-877	IP20
21630-878	IP20
21630-879	IP20
21630-880	IP20
21630-881	IP20
21630-882	IP20
21630-883	IP20

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER