


FRONT PANEL EMC TEXTILE SHIELDING KIT, -40 UP TO +85°C



The textile EMC gaskets are inserted into a slot on the right hand side of the U-shaped front panels. The gaskets are glued to the front panel. For an expanded temperature range up to +85°C.

CERTIFICATIONS



CARACTERÍSTICAS

Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.

Profile seal is bonded onto the contact surface of the 19" bracket or of the rear angle and sets up the conductive connection to the U-shaped front panels

Temperature range -40 °C ... +85 °C

ESPECIFICACIONES

Table 1/1

Número de catálogo	Package Quantity	Product Type	Product Family	Works With	Rack Height
21102-857	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	2 U

Número de catálogo	Package Quantity	Product Type	Product Family	Works With	Rack Height
21102-853	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	3 U
21102-854	100	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	3 U
21102-858	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	4 U
21102-978	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	5 U
21102-855	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	6 U
21102-856	100	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	6 U
21102-859	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	9 U

ADDITIONAL PRODUCT DETAILS

EMC gaskets (textile) are required for shielding the front panels.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones

corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER