


## 19" FRONT PANEL, VENTED

Vented front panels allows heat dissipation through holes.



### CERTIFICATIONS



### CARATTERISTICHE

Vented front panels (Aluminum ) allows heat dissipation

### SPECIFICHE

**Accessory Type:** Front panel

Table 1/3

Codice a catalogo	Tipo	Montaggio	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30118-962	19" Front Panel	Screw-on Front	Painted	Painted		No
30702-044	19" Front Panel	Screw-on Front	Raw	Conductive		No
30702-047	19" Front Panel	Screw-on Front	Anodized	Anodized	Yes	No
30702-056	19" Front Panel	Screw-on Front	Painted	Painted		No
30118-963	19" Front Panel	Screw-on Front	Painted	Painted		No
30118-964	19" Front Panel	Screw-on Front	Painted	Painted		No
30702-045	19" Front Panel	Screw-on Front	Raw	Raw		No

<b>Codice a catalogo</b>	<b>Tipo</b>	<b>Montaggio</b>	<b>Front Finish</b>	<b>Rear Finish</b>	<b>Treated Edges</b>	<b>EMC Shielding</b>
30702-046	19" Front Panel	Screw-on Front	Raw	Raw		No
30702-048	19" Front Panel	Screw-on Front	Anodized	Anodized	Yes	No
30702-049	19" Front Panel	Screw-on Front	Anodized	Anodized	Yes	No
30702-057	19" Front Panel	Screw-on Front	Painted	Painted		No
30702-058	19" Front Panel	Screw-on Front	Painted	Painted		No

Table 2/3						
<b>Codice a catalogo</b>	<b>Rack Width</b>	<b>Product Type</b>	<b>Altezza (H)</b>	<b>Works With</b>	<b>Rack Height</b>	<b>Quantità per confezione</b>
30118-962	95HP	Front Panel	43.6mm	Cabinet, Wallmount Cases, 19" cases	1U	1
30702-044	95HP	Front Panel	43.6mm	Cabinet, Wallmount Cases, 19" cases	1U	1
30702-047	95HP	Front Panel	43.6mm	Cabinet, Wallmount Cases, 19" cases	1U	1
30702-056	95HP	Front Panel	43.6mm	Cabinet, Wallmount Cases, 19" cases	1U	1
30118-963	95HP	Front Panel	88.1mm	Cabinet, Wallmount Cases, 19" cases	2U	1
30118-964	95HP	Front Panel	132.5mm	Cabinet, Wallmount Cases, 19" cases	3U	1
30702-045	95HP	Front Panel	88.1mm	Cabinet, Wallmount Cases, 19" cases	2U	1
30702-046	95HP	Front Panel	132.5mm	Cabinet, Wallmount Cases, 19" cases	3U	1


Codice a catalogo	Rack Width	ProductType	Altezza (H)	Works With	Rack Height	Quantità per confezione
30702-048	95HP	Front Panel	88.1mm	Cabinet, Wallmount Cases, 19" cases	2U	1
30702-049	95HP	Front Panel	132.5mm	Cabinet, Wallmount Cases, 19" cases	3U	1
30702-057	95HP	Front Panel	88.1mm	Cabinet, Wallmount Cases, 19" cases	2U	1
30702-058	95HP	Front Panel	132.5mm	Cabinet, Wallmount Cases, 19" cases	3U	1

Table 3/3					
Codice a catalogo	Finitura	Materiale	Colore	Codice colore	Larghezza (W)
30118-962	Powder Coated	Aluminum	Light Grey	RAL 7021	483mm
30702-044	Anodized	Aluminum			483mm
30702-047	Anodized	Aluminum			483mm
30702-056	Powder Coated	Aluminum	Black Grey	RAL 7035	483mm
30118-963	Anodized	Aluminum	Light Grey	RAL 7021	483mm
30118-964	Powder Coated	Aluminum	Light Grey	RAL 7021	483mm
30702-045	Anodized	Aluminum			483mm
30702-046	Anodized	Aluminum			483mm
30702-048	Anodized	Aluminum			483mm
30702-049	Anodized	Aluminum			483mm
30702-057	Powder Coated	Aluminum	Black Grey	RAL 7035	483mm
30702-058	Powder Coated	Aluminum	Black Grey	RAL 7035	483mm

## ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

## DIAGRAMS



## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**