


JOINT BOND MOLD PAIR ONLY, SIGNAL



CARATTERISTICHE

Pair of replacement molds designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

SPECIFICHE

Materiale: Graphite

Table 1/2

Codice a catalogo	Stile terminale collegamento	Tipo di rotaia	Prodotto	Handle Clamp	Diametro esterno conduttore, nominale	Stile saldatore
SBM456	3/4" XS	85 lb to 141 lb T-Rail Sections	Mold and Mold Cleaning Tool		4.76mm	T6, T7
SBM456M	3/4" XS	85 lb to 141 lb T-Rail Sections	Mold only		4.76mm	T6, T7
SBS5838	3/4" Tab	85 lb to 141 lb T-Rail Sections	Mold and Mold Cleaning Tool		4.76mm	T6, T7
SBS5838M	3/4" Tab	85 lb to 141 lb T-Rail Sections	Mold only	C105B, Sold Separately	4.76mm	T6, T7
SBS5839	1" Tab	85 lb to 141 lb T-Rail Sections	Mold and Mold Cleaning Tool		4.76mm	T6, T7
SBS5839M	1" Tab	85 lb to 141 lb T-Rail Sections	Mold only		4.76mm	T7

Codice a catalogo	Stile terminale collegamento	Tipo di rotaia	Prodotto	Handle Clamp	Diametro esterno conduttore, nominale	Stile saldatore
SBS925	Head Free	Head-Free Rail	Mold and Mold Cleaning Tool		4.76mm	T6, T7
SBS925M	Head Free	Head-Free Rail	Mold only	C105B, Sold Separately	4.76mm	T6, T7
SBB492	Head Free	Head-Free Rail	Mold and Mold Cleaning Tool		7.94mm	T6, T7
SBB492M	Head Free	Head-Free Rail	Mold only		7.94mm	T6, T7
SBS898	1" Tab	85 lb to 141 lb T-Rail Sections	Mold and Mold Cleaning Tool		7.94mm	T6, T7
SBS898M	1" Tab	85 lb to 141 lb T-Rail Sections	Mold only		7.94mm	T6, T7
SBTBT71YM	1" Tab	85 lb to 141 lb T-Rail Sections	Mold only		8.43mm	T7

Table 2/2		
Codice a catalogo	Materiale per saldatura	Dimensioni conduttore
SBM456	SB25 x 2, Sold Separately	3/16" Bondstrand
SBM456M	SB25 x 2, Sold Separately	3/16" Bondstrand
SBS5838	SB25 x 2, Sold Separately	3/16" Bondstrand
SBS5838M	SB25, Sold Separately	3/16" Bondstrand
SBS5839	SB25 x 2, Sold Separately	3/16" Bondstrand
SBS5839M	SB25, Sold Separately	3/16" Bondstrand
SBS925	SB25 x 2, Sold Separately	3/16" Bondstrand
SBS925M	SB25, Sold Separately	3/16" Bondstrand
SBB492	SB32 x 2, Sold Separately	5/16" Bondstrand
SBB492M	SB32 x 2, Sold Separately	5/16" Bondstrand
SBS898	SB32 x 2, Sold Separately	5/16" Bondstrand
SBS898M	SB32 x 2, Sold Separately	5/16" Bondstrand
SBTBT71YM	SB32, Sold Separately	#1 Concentric

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



WARNING: This product can expose you to chemicals including silica, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER