


GUIDE RAIL ACCESSORIES FOR HEAVY PCBs, EXTRA STRONG



This reinforced guide rail for heavy PCBs of the type accessory, forms a reliable interface between the subrack mechanics and the sub-assemblies. The guide rails can additionally be bolted to the horizontal

CERTIFICATIONS



FEATURES

For especially heavy PCBs, plug-in units or frame type plug-in units

Mounting, for bolting to type H (heavy) and type R (rugged) horizontal rails only

Aluminium profile

SPECIFICATIONS

Table 1/2

Numero catalogo	Board Depth	Product Type	Product Family	Works With	Tipo	Colore
34562-884	340 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver

Numero catalogo	Board Depth	ProductType	Product Family	Works With	Tipo	Colore
34562-885	400 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver
34562-881	160 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver
34562-883	280 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver
34562-882	220 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver
34564-881	160 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver
34564-882	220 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver

Numero catalogo	Board Depth	ProductType	Product Family	Works With	Tipo	Colore
34564-883	280 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver
34564-884	340 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver
34564-885	400 mm	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, Chassis	Per applicazioni pesanti	Silver

Table 2/2		
Numero catalogo	Materiale	Groove Width
34562-884	Alluminio	2
34562-885	Alluminio	2
34562-881	Alluminio	2
34562-883	Alluminio	2
34562-882	Alluminio	2
34564-881	Alluminio	2.5
34564-882	Alluminio	2.5
34564-883	Alluminio	2.5
34564-884	Alluminio	2.5
34564-885	Alluminio	2.5

ADDITIONAL PRODUCT DETAILS

Delivery is exclusively in standard pack quantity.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER